

# 02 08 225 US

## High Leverage Combination Pliers



- 35 % less effort required than with conventional combination pliers
- easier work due to optimised leverage
- with cutting edges (hardness approx. 63 HRC) for soft and hard wire and piano wire
- long cutting edges for thicker cables
- with gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, oil-hardened

|   |  |
|---|--|
| <b>Product Number</b>   | 02 08 225 US   |
| <b>EAN</b>  | 843221003661   |
| <b>Pliers</b>   |  |
| <b>Head</b>   | polished   |
| <b>Handles</b>  | insulated with two-colour dual component handles, VDE-tested |
| <b>Insulation standard</b>  | IEC 60900 DIN EN 60900                                       |
| <b>hard wire Ø mm</b>   | 3  |
| <b>piano wire Ø mm</b>  | 2,5  |
| <b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b> | 14   |
| <b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>  | 25   |
| <b>Net weight g</b>   | 401  |
| <b>Length mm</b>  | 225  |

*technical change and errors excepted*