

FROGTAPE® BRAND DELICATE SURFACE PAINTER'S TAPE



TYPICAL APPLICATIONS

- For interior use on freshly painted surfaces (24 hours old), faux finishes, primed wallboard and wallpaper

PRODUCT FEATURES

- Low adhesion
- Exclusive PaintBlock® Technology
- Prevents paint bleed to deliver very sharp lines
- 60-day clean removal
- Housed in a plastic canister to protect tape edges

CONSTRUCTION

Overall Grade/Function: Delicate surface
 Backing: Washi paper
 Adhesive: Acrylic-based

STANDARD WIDTH(S)

24 mm 36 mm 48 mm

STANDARD LENGTH(S)

55 m
 Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	23 lbs/in width	40.3 N/10 mm
Adhesion to Stainless Steel	14 oz/in width	1.53 N/10 mm
Thickness	3.6 mils	0.09 mm
Elongation	4.5%	4.5%

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

