



Lineman's Pliers, Heavy-Duty Side Cutting, 8-Inch



These lineman's pliers are made of custom, US-made tool steel and feature combination polished and black-oxide finish plus plastic-dipped handles for comfort and ease of identification. 2000 series knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting and gripping power than other plier designs. Cutting knives are induction hardened for long life. The hot-riveted joint ensures smooth action and no handle wobble. Streamlined design with sure-gripping, cross-hatched knurled jaws. Unique handle tempering helps absorb the "snap" when cutting wire. The head is precision-hardened for on-the-job toughness.

Specifications

Type:	Side Cutting Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire
Overall Length:	8.59" (21.8 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.44" (3.7 cm)
Jaw Width:	1.109" (2.8 cm)	Jaw Thickness:	0.6" (1.5 cm)
Jaw Capacity:	1.58" (4 cm)	Knife Length:	0.719" (1.8 cm)
Cut Style:	Cross Cut	Joint Type:	Hot Riveted
Handle Color:	Light Blue	Handle Finish:	Plastic-Dipped
Handle Length:	6.156" (15.6 cm)	Insulated:	No
Tether Capable:	No	Weight:	13.6 oz (386 g)