



**NOBLES**<sup>®</sup>  
ENGINEERED BY TENNANT COMPANY

**SPEED SCRUB**<sup>®</sup> 15 inch battery  
Cordless, compact and can clean anytime



# Cordless cleaning. Anytime. Anywhere.

## The Speed Scrub® 15 inch battery

### Cordless design for safety and cleaning flexibility

Eliminates cord hazards and constraints for easy cleaning any time of day.

### Recharge battery multiple times a day

Compared to standard batteries, optional lithium-ion battery technology lasts up to 20 times longer in high frequency, quick charge applications.

### Compact and maneuverable

Clean small, congested areas safely and efficiently without disturbing customers, patients, students or employees.



## Many applications

### 1. Retail

Perfect for convenience stores, check out aisles, food prep areas and quick clean-ups anytime.



### 2. Healthcare

Compact and quiet for use in patient rooms, cafeterias and touch-ups in other areas.



Built to be **tough**. Made to be **easy**.



## Two Battery Options to Match Your Needs — AGM or Lithium-ion

AGM battery provides up to 45 minutes of high performance cleaning which is best suited to single daily use.

Lithium-ion batteries provide up to 60 minutes of run time, thrive on multiple use/charge applications, and are lighter and provide longer run time than standard batteries.

### Battery Recommendation Matrix

APPLICATION	AGM	LITHIUM-ION
1-2 charges per day (standard cleaning)	✓	✓
3 or more charges per day		✓
Multiple users/ departments daily		✓
“Utility Tool” usage – mop and bucket approach for cleaning		✓
Seasonal clean up issues (snow/salt, sand, rain, etc.) tracked into facility		✓
Frequent spills or touch-ups needed		✓



- 3. Education**  
Easily reach under tables and desks with ultra low profile machine and Insta-Adjust™ handle.





## OPTIMIZE CLEANING PERFORMANCE WITH TENNANTTRUE®

Maximize the uptime and life of your Nobles brand equipment with TennantTrue® parts and service. Benefit from the unmatched knowledge of our team of over 400 factory-trained and certified Tennant Service Reps. Improve productivity with quality parts and supplies that are designed to enhance equipment results.

Depend on TennantTrue® to help you maximize the effectiveness of cleaning operations.

**Engineered by Tennant Company, the Nobles Speed Scrub® 15 inch battery is a smart, reliable choice for your anytime cleaning needs.**

### Warranty

3 years/2500 hours on parts and labor. 10 years on rotationally molded polyethylene tanks. AGM battery pro-rated for 6 months; lithium-ion battery pro-rated for 24 months.

### Nobles

701 North Lilac Drive  
Minneapolis, MN 55422

800.553.8033  
763.540.1200  
f: 763.513.2112

www.nobles.com  
nobles@tennantco.com

Specifications		
Cleaning path	15 in	380 mm
Solution tank capacity	2.5 gal	9.5 L
Productivity (per hour)		
Theoretical max	14,875 ft <sup>2</sup>	1,382 m <sup>2</sup>
Estimated coverage*	7,743 ft <sup>2</sup>	719 m <sup>2</sup>
Solution flow rate	0.10 gpm	0.37 lpm
Scrub motors	0.65 hp	0.49 kW
Scrub motor speed	900 rpm (@ brush)	
Brush down pressure	38 lb	17 kg
Brush size	3.5 in	89 mm
Recovery tank capacity (includes demisting chamber)	3.4 gal	12.9 L
Vacuum fan	1-stage, 0.5 hp / 0.38 kW	
Vacuum system sealed water lift	25 in	635 mm
Battery power system (lithium-ion or AGM)	12.8 VDC	
Battery run time (lithium-ion / AGM)	up to 60 min / up to 45 min	
Machine net weight (lithium-ion / AGM)	110 lb / 126 lb	50 kg / 57 kg
Height		
Base (to top of cover)	20 in	510 mm
Base (folded handle for storage)	23.8 in	600 mm
With handle up	34 in	860 mm
Sound level (operator's ear)	68 dBA	

\*Estimated coverage rates use the practical speed and empty/fill time standards from the 2004 ISSA Cleaning Times handbook.