



## STS 325 R

### Hacksaw for pipes up to Ø 24 in

Pneumatic hacksaw for pipes and profiled sections.

Product number: 7 534 08 13 00 0

## Details

- > Ideally suited for cutting pipes and profiles made of steel, cast iron, autoclaved aerated concrete, and plastics.
- > Clamp and feed device available for profiles and pipes from Ø 3-1/8 in [80 mm] to Ø 24 in [400 mm].
- > Adjustable clamping devices permit mitre cuts up to 45° as well.
- > Clamp and feed device available.
- > Adjustable clamping fixtures.
- > \* Chain extension available.

## Price includes

- ✓ 2 saw blades (type 063)
- ✓ 1 wrench set
- ✓ 1 handle
- ✓ 1 hose coupling

## Product feature

- ✓ aus\_druckluftantrieb



## Technical data

### TECHNICAL DATA

Operating pressure

87 [6.0] psi[bar]

Air consumption

51.2 [1.45] cfm[m<sup>3</sup>/min]

Power output

1,100 W

Strokes

330 spm

Stroke of blade

2-1/4 [60] in[mm]

Pipes up to Ø

17-1/4 [440] \* in[mm]

Profiles up to W x H

11-1/2 [290] x 19-3/4 [500] in[mm]

Weight according to EPTA

15.87 [7.20] lbs[kg]