

Professional Electrician Pliers



- Professional quality tools for maximum life and performance
- Forged of vanadium alloy steel provides excellent durability
- Precision mated blades for easy cutting
- Smart-Grip™ textured grips provide a sure grip and are impervious to gas, oil, and hydraulic fluid
- Smart-Grip™ handle ends are color-coded and have FastFinder™ letter icons for quick identification

Made in U.S.A.



MADE IN THE U.S.A.

At a time when some companies are taking manufacturing jobs overseas, our commitment to American-made quality and homegrown manufacturing has never been stronger. At IDEAL Electrical, we are committed to American quality and the American electrician. With forging facilities in Colorado Springs, CO and our efficient manufacturing

and distribution center in Sycamore, IL, IDEAL® Electrical pliers are crafted with American steel right here in the U.S.A. for quality and performance you can trust. IDEAL Electrical is proud to be part of IDEAL INDUSTRIES INC., a family-owned, blue-collar American company that believes in serving the hardest working tradesmen in the world.



Colorado Springs, CO



Sycamore, IL



Pottstown, PA


Professional Electrician Pliers

Proudly Made in the U.S.A.

Made in U.S.A.




Smooth nose
Slides in/out of pouch without scratch or tears



Knife-to-knife cutting blades



High-leverage hot-riveted construction requires less cutting force



Fine grained cross-hatched nose grabs wire without damage to fine strands



Large head for superior force and optimum fit to ream conduit

American made custom alloyed steel

Hot forged frames with black oxide for lifetime of professional use



Leopard spots sweat-relief pattern in grips

Sure-Grip™ textured grips are impervious to hydraulic fluids, gasoline, oils and other chemicals



Fish tape puller



Crimp die



Color-coding and FastFinder™ letter markers on the inside of our Smart-Grip™ handles provide quick tool identification, even by touch



Linesman

Tongue & Groove

Crimper

Cable Cutter

Long Nose

Diagonal



Dipped Grip

Heavy duty textured PVC grips provide superior comfort and improved grip for everyday commercial use. The durable dipped grips bond to the steel plier handles during our proprietary immersion gripping process.

- Heavy-duty, textured grip
- Excellent fit, form, and functionality
- Dipped hot for uniform shape and optimum adhesion and perfect form

Smart-Grip™

These pliers provide professional results for everyday use. These tools are the workhorse of electrical pliers; they are rugged yet precise, providing exceptional durability, easy cutting and a lifetime of quality use.

- Color-coded and FastFinder™ icons for quick identification and organization
- Raised letter icons facilitate identification of tool with just the quickest touch
- Leopard-spot pattern, molded into the Santoprene® grip for improved control on hot work sites
- Grips are impervious to gas, oil, and hydraulic fluid.



Insulated Grip

The IDEAL® insulated tool line creates a perfect blend of safety, comfort and precision functionality. Each tool features double insulated Santoprene® handles with a soft, easy-to-grip outer surface. In addition to the ergonomic qualities found in our tools, the insulated coating process acts as an 'at-a-glance' safety check. If the orange outer coating reveals any of the inner yellow surface, an electrician will know that this tool needs to be replaced.

- Dual-layer injection molded grips provide 1000V protection from electrical shock
- UL logo on every plier validates each tool is individually hot tested and approved prior to shipping
- Meets or exceeds ASTM standards
- Leopard-spot pattern, molded into the Santoprene® grip for improved control on hot work sites
- Grips are impervious to gas, oil, and hydraulic fluid



Santoprene is a registered trademark of Exxon Mobil Corporation.

Not all Insulated Grip tools are made in the U.S.A.

The Full-Line of IDEAL® Pliers

Dipped Grip

Smart-Grip™

Insulated Grip

Linesman Pliers

Feature knife-to-knife cutting blades, high leverage pivots, cam-action fish tape puller and dual crimp dies.



Multi-Crimp Tools

Cuts, crimps and splices 10-22 AWG wires for insulated and non-insulated crimp connectors.



Diagonal Cutters

Straight handle Smart-Grip™ model features an integral spring which can be deployed or stored as needed. Angled head model is shaped for optimum staple pulling leverage.

*Not pictured: 35-028 Non-angled head, 35-3029 Angled Head



Cable Cutters

Precision ground, by-pass cutter blades provide smooth, easy cuts up to 2/0 copper or aluminum.



Long-Nose

Narrow profile head for working in tight spaces.

*Not Pictured: 35-036 (6 in.)



Tongue & Groove

Flush-ground rivets provide greater access into tight spaces and never loosen up.

*Not pictured: 35-426 (7 in.), 35-430 (10-1/2 in.), 35-440 (13 in.)



Electrician Tool Kits



16-Piece Set
35-800



13-Piece Set
35-790



17-Piece Set
35-809



5-Piece Set
35-5792



16-Piece Set
35-808



6-Piece Set
35-794



12-Piece Set
35-5805



4-Piece Set
35-5799

See website or catalog for complete kit descriptions.



IDEAL INDUSTRIES, INC.
1375 Park Avenue, Sycamore, IL 60178, USA

International offices:
Australia • Brazil • Canada • China • Germany • Mexico • UK