



### WELDING APPAREL

#### Select Your Fabric

Fabric	Description	Cost	Durability	Protection Level
<b>Classic FR Cotton</b>	Ideal for everyday use. Nine ounce, flame-resistant, pre-shrunk fabric features quality material without compromising your bottom line.	\$	•	Light-Duty
<b>INDURA® FR Cotton</b>	The Indura brand name is derived from “Industrial Durability.” Indura is a 100% cotton, flame-resistant fabric, guaranteed for the life of the garment. Indura will self-extinguish and will not ignite, but it can burn.	\$\$	••	Light-Duty
<b>Combo</b>	Perfect mix of top-grain leather and Indura FR cotton, providing additional protection in high-exposure areas.	\$\$\$	•••	Medium-Duty
<b>WeldX™</b>	Extreme flame-resistant properties won't burn, melt, ignite or shrink - repelling sparks, spatter and other molten metals. Chromium free for easy disposal. Machine washable, retains FR properties. A Miller exclusive.	\$\$\$\$	••••	Medium-Duty
<b>Leather</b>	Top-grain pigskin leather withstands sparks and spatter for long-term industrial use.	\$\$\$\$	•••••	Heavy-Duty

#### Classic FR Cotton Jacket Sizing & Part Numbers

	S	M	L	XL	2XL	3XL	4XL	5XL
<b>Part #</b>	244749	244750	244751	244752	244754	244755	244756	244758
<b>Chest Width</b>	42 in	46 in	50 in	54 in	58 in	62 in	66 in	70 in
<b>Sleeve Length</b>	31 in	32 in	33 in	34 in	35 in	36 in	37 in	38 in
<b>Shoulder Width</b>	15.5 in	17 in	18.5 in	20 in	21.5 in	23 in	24.5 in	26 in

#### INDURA® FR Cotton Men's Jacket Sizing & Part Numbers

	S	M	L	XL	2XL	3XL	4XL	5XL
<b>Part Number</b>	258095	258097	258098	258099	258100	258101	258102	258104
<b>Chest Width</b>	44 in	48 in	52 in	56 in	60 in	64 in	68 in	72 in
<b>Sleeve Length</b>	32 in	33 in	34 in	35 in	36 in	37 in	38 in	39 in
<b>Shoulder Width</b>	18 in	19 in	20 in	21 in	22 in	24 in	25 in	27 in

### INDURA® FR Cotton Women's Jacket Sizing & Part Numbers

	<b>S</b>	<b>M</b>	<b>L</b>	<b>XL</b>	<b>2XL</b>
<b>Part Number</b>	264379	264380	264381	264382	264383
<b>Shoulder Width</b>	14 in	16 in	18 in	19 in	20 in
<b>Chest Width</b>	19 in	21 in	23 in	25 in	26 in
<b>Sleeve Length</b>	32 in	33 in	34 in	36 in	38 in
<b>Torso Length</b>	22 in	25 in	26 in	27 in	27 in

### Combo Jacket Sizing & Part Numbers

	<b>S</b>	<b>M</b>	<b>L</b>	<b>XL</b>	<b>2XL</b>	<b>3XL</b>	<b>4XL</b>	<b>5XL</b>
<b>Part Number</b>	231080	231081	231082	231083	231084	231085	231086	231087
<b>Chest Width</b>	44 in	46 in	50 in	52 in	58 in	62 in	65 in	69 in
<b>Sleeve Length</b>	32 in	33 in	34.5 in	35 in	37 in	37.5 in	39.5 in	40 in
<b>Shoulder Width</b>	17.5 in	18 in	19 in	20 in	22 in	23 in	24 in	25 in

### Leather Jacket Sizing & Part Numbers

	<b>S</b>	<b>M</b>	<b>L</b>	<b>XL</b>	<b>2XL</b>	<b>3XL</b>	<b>4XL</b>	<b>5XL</b>
<b>Part Number</b>	231088	231089	231090	231091	231092	231093	231094	231095
<b>Chest Width</b>	44 in	48 in	52 in	56 in	60 in	64 in	68 in	72 in
<b>Sleeve Length</b>	32 in	33 in	34 in	35 in	36 in	37 in	38 in	39 in
<b>Shoulder Width</b>	18 in	19 in	20 in	21 in	22 in	24 in	25 in	27 in

### WeldX™ Jacket Sizing & Part Numbers

	<b>S</b>	<b>M</b>	<b>L</b>	<b>XL</b>	<b>2XL</b>	<b>3XL</b>	<b>4XL</b>	<b>5XL</b>
<b>Part Number</b>	247114	247115	247116	247117	247118	247119	247120	247121
<b>Chest Width</b>	42 in	46 in	50 in	54 in	58 in	62 in	66 in	70 in
<b>Sleeve Length</b>	32 in	33 in	34 in	35 in	36 in	37 in	38 in	39 in
<b>Shoulder Width</b>	19 in	20 in	21 in	22 in	23 in	24 in	25 in	26 in