



Main

Range of product	MD
Product or component type	Motor Disconnect Switch
Line Rated Current	30 A
Motor power hp	7.5 hp 220/240 V AC 20 hp 440/480 V AC 25 hp 600 V AC
NEMA degree of protection	NEMA 4X
Product certifications	UL listed

Complementary

Environment

Offer Sustainability

Not Green Premium product	Not Green Premium product
Compliant - since 1610 - Schneider Electric declaration of conformity	Compliant - since 1610 - Schneider Electric declaration of conformity

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.