



**MCR
SAFETY**

N9690HV

Ninja

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Ice Hi Vis features a 15 gauge Hi Vis lime nylon shell with a 7 gauge acrylic terry interior liner. Hi Vis Lime HPT coated palm and fingertips.

FEATURES:

- Acrylic Terry liner for insulation / warmth.
- Hi Visibility HPT repels liquids while providing strong wet or dry grip
- Over the knuckle coating for added protection
- Coating remains soft in temperatures as low as -58 F
- CE Score 3232

APPLICATIONS:

Cold storage applications, Commercial fishing, Frozen food packaging, Agriculture, Carpentry, Construction, Flagman, HVAC, Landscaping, Warehousing



TECHNICAL DATA FOR: N9690HV

Series	Ninja	EN 388 : CE Score - Abrasion	3
Material Group	Strings	EN 388 : CE Score - Cut	2
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	2
Gauge	15 / 7 Gauge	ANSI Cut	ANSI Cut A3
Material	Nylon / Acrylic	ANSI Puncture	ANSI Puncture 2
Insulated	Insulated	ANSI Abrasion	ANSI Abrasion 3
Lining	Acrylic	ANSI Contact Heat	Level 2 (Applications less than 284 degrees F)

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N9690HV

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9690HVL	Large	10.228	5.629	N/A	25.920 lb.	4.320
N9690HVM	Medium	9.843	5.355	N/A	25.998 lb.	4.333
N9690HVXL	X - Large	11.024	5.827	N/A	28.062 lb.	4.677
N9690HVXXL	XX - Large	11.417	6.141	N/A	28.986 lb.	4.831

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved