

ULTIMA®
ULTIMA® High NRC

Square Lay-in
fine texture



▲ Ultima® Square Lay-in panels with Prelude® XL® 15/16" suspension system

Smooth-texture panels that are washable, impact- and scratch-resistant with a non-directional visual. Offer both Sustain® and Total Acoustics® panel performance for flexible spaces.

KEY SELECTION ATTRIBUTES

- Get total noise control and floor plan versatility with Total Acoustics® ceiling panels: NRC + CAC = Total Acoustics performance
- Ultima® panels are part of the Sustain® portfolio, and meet the most stringent industry sustainability compliance standards today
- CleanAssure™ family of products – includes disinfectable panels, suspension systems, and trim
- Mold- and mildew-resistant surface
- Smooth, clean, durable finish – Washable, Impact-resistant, Scratch-resistant, Soil-resistant
- Ceiling-2-Ceiling™ Post-consumer Recycled Content options: items 1910HRC, 1913HRC 71% Pre-consumer; 15% Post-consumer
- USDA-Certified Biobased Product – 95%
- Available with AirGuard™ coating – actively removes formaldehyde from indoor air

- Item 1910 available with Create!™ printed images and patterns
- Non-directional visual reduces scrap and installation time
- Compatible with the TechZone® Ceiling Systems
- 30-Year Limited System Warranty against visible sag
- 10-Year replacement panel available for items 1910, 1913



COLOR



White (WH)

DETAILS



1. Ultima® Square Lay-in
2. Ultima® Square Lay-in with Prelude® XL® 15/16" suspension system

CAD/Revit® drawings at:
armstrongceilings.com/cadrevit



DESIGNflex®
A New World of Choice
for Ceiling Systems

plus capabilities
to do more



armstrongceilings.com/capabilities
See more photos at:
armstrongceilings.com/photogallery

TYPICAL APPLICATIONS

- Offices – closed spaces for privacy and confidentiality; open spaces for focus, collaboration, and teaming
- Healthcare – assists in addressing HIPAA, HCAHPS, and FGI acoustical requirements
- Classrooms
- Corridors
- Lobbies/reception areas
- Department stores/retail

ULTIMA® ULTIMA® High NRC

Square Lay-in
fine texture



USDA
CERTIFIED
BIOBASED
PRODUCT
PRODUCT 95%

Declare.

SUSTAIN®
High Performance
Sustainable Ceiling Systems

GREENGUARD
Gold Certified
(details below)

LEED®
WELL™ LBC

UP TO 87% RECYCLED CONTENT

Calculate sustainability with GreenGenie™
armstrongceilings.com/greengenie

LOCATION DEPENDENT

VISUAL SELECTION

armstrongceilings.com/catdwgs	Susp. Dwg.	Item No.	Dimensions (Inches)
ULTIMA® High NRC 15/16" Square Lay-in 	1	1940	24 x 24 x 7/8"
		1943	24 x 48 x 7/8"
		1432	24 x 60 x 7/8"
		1435	24 x 72 x 7/8"
7/8" Thick – 15/16" Square Lay-in			
Made-to-Order Sizes	Width	Length	
Visit the product page online and see "Configure an Item" to verify capabilities. Questions? email Techline@armstrongceilings.com	4" – 6"	12" – 72"	N/A
	6-1/2" – 30"	12" – 72"	N/A
	30-1/2" – 48"	4" – 30"	N/A

1 Ctn Min
FASTSIZE
3 WEEKS
order to ship

PERFORMANCE SELECTION

Dots represent high level of performance.

UL Classified Acoustics	Total Acoustics ¹	Articulation Class	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	CleanAssure™ Disinfectable Panels	DURABILITY	Recycle Program	30-Yr Warranty			
NRC + CAC =	NRC CAC	AC	Fire	Light	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	Fog	Wash	Impact	Scratch	Soil	Recycle Program	30-Yr Warranty
0.80 + 35 =	BEST (170)	Class A	0.87	•	•	•	•	•	•	•	•	•	•	•
0.80 + 35 =	BEST (170)	Class A	0.87	•	•	•	•	•	•	•	•	•	•	•
0.80 + 35 =	BEST (170)	Class A	0.87	•	•	•	•	•	•	•	•	•	•	•
0.80 + 35 =	BEST (170)	Class A	0.87	•	•	•	•	•	•	•	•	•	•	•
N/A	N/A	N/A	N/A	Class A	0.87	•	•	•	•	•	•	•	•	•

MORE ITEMS ►

¹ Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.
GOOD (NRC 0.60-0.65; CAC 35+) BETTER (NRC 0.70-0.75; CAC 35+) BEST (NRC 0.80+; CAC 35+)

SUSPENSION SYSTEMS

15/16" Prelude®
Blizzard White – Suspension System Finish
A color and texture coordinated suspension system to complement Ultima® ceiling panels for a monolithic look and feel.

PHYSICAL DATA

Material
Wet-formed mineral fiber with DuraBrite® acoustically transparent membrane

Surface Finish
DuraBrite scrim with factory-applied latex paint

Fire Performance
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

ASTM E1264 Classification
Type IV, Form 2, Pattern E
Fire Class A

Humidity/Sag Resistance
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications.

Anti-Mold/Mildew
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

VOC Emissions
GREENGUARD Gold Certified
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

Acoustical Performance
CAC testing conducted using Prelude® XL® suspension system.

Primary (Embodied) Energy
See all LCA information on our EPDs.

High Recycled Content
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines. HRC items contain 15% or greater post-consumer recycled ceilings.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS
UL.COM/GG
UL 2818



Insulation Value
R Factor – 2.2 (BTU units)
R Factor – 0.39 (Watts units)

Cleaning and Disinfecting
Cleaning and CDC recommended disinfecting options available on armstrongceilings.com/cleaning

30-Year Performance Guarantee & Warranty
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty

Weight; Square Feet/Carton
1940 – 1.14 lbs/SF; 40 SF/ctn
1943 – 1.125 lbs/SF; 48 SF/ctn
1432 – 1.05 lbs/SF; 60 SF/ctn
1435 – 1.04 lbs/SF; 72 SF/ctn

Minimum Order Quantity
1 carton

Metric Items Available
1940M, 1943M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.



ULTIMA® ULTIMA® High NRC

Square Lay-in
fine texture



USDA
CERTIFIED
BIOBASED
PRODUCT
PRODUCT 95%

SUSTAIN®
High Performance
Sustainable Ceiling Systems

GREENGUARD
Gold Certified
(details below)

Declare.®

LEED®
WELL™
LBC

UP TO **87%** RECYCLED CONTENT

- energy management
- construction waste mgmt
- regional materials
- design for flexibility
- EPD
- recyclable/extended producer resp.
- biobased materials
- recycled content
- sourcing of raw materials
- material ingredient reporting
- low emitting materials
- lighting quality
- acoustics

LOCATION DEPENDENT

Calculate sustainability with GreenGenie™
armstrongceilings.com/greengenie

VISUAL SELECTION

armstrongceilings.com/catdws	Susp. Dwg.	Item No.	Dimensions (Inches)
ULTIMA® 15/16" Square Lay-in		1420	6 x 48 x 3/4"
		1425	6 x 60 x 3/4"
		1990	12 x 48 x 3/4"
		1991	12 x 60 x 3/4"
		1992	12 x 72 x 3/4"
1910 1910HRC*		1910	24 x 24 x 3/4"
		1910HRC*	24 x 24 x 3/4"
		1913 1913HRC*	24 x 48 x 3/4"
		1913HRC*	24 x 48 x 3/4"
1984 1980		1984	24 x 60 x 3/4"
		1980	24 x 72 x 3/4"

HRC items not included in made-to-order panels.

1 Ctn Min
FASTSIZE
3 WEEKS
order to ship

Made-to-Order Sizes	Width	Length
Visit the product page online and see "Configure an Item" to verify capabilities. Questions? email Techline@armstrongceilings.com	4" – 6"	12" – 72"
	6-1/2" – 30"	12" – 72"
	30-1/2" – 48"	4" – 30"

¹ Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.
GOOD (NRC 0.60-0.65; CAC 35+) **BETTER** (NRC 0.70-0.75; CAC 35+) **BEST** (NRC 0.80+; CAC 35+)

PERFORMANCE SELECTION

Dots represent high level of performance.

UL Classified Acoustics	Total Acoustics ¹	Articulation Class	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	CleanAssure™ Disinfectable Panels	DURABILITY				Recycle Program
NRC + CAC	NRC CAC							Fog	Wash	Impact	Scratch	Soil	30-Yr Warranty
N/A	N/A	N/A	Class A	0.88									
N/A	N/A	N/A	Class A	0.88									
0.65*	N/A	N/A	Class A	0.88									
0.65*	N/A	N/A	Class A	0.88									
0.65*	N/A	N/A	Class A	0.88									
0.75	35	BETTER	Class A	0.88									
0.75	35	BETTER	Class A	0.88									
0.75	35	BETTER	Class A	0.88									
0.75	35	BETTER	Class A	0.88									
N/A	N/A	N/A	Class A	0.88									

SUSPENSION SYSTEMS

15/16" **Blizzard White – Suspension System Finish**
A color and texture coordinated suspension system to complement Ultima® ceiling panels for a monolithic look and feel.

PHYSICAL DATA

Material
Wet-formed mineral fiber with DuraBrite® acoustically transparent membrane

Surface Finish
DuraBrite scrim with factory-applied latex paint

Fire Performance
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

ASTM E1264 Classification
Type IV, Form 2, Pattern E
Fire Class A

Humidity/Sag Resistance
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications.

Anti-Mold/Mildew
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

VOC Emissions
GREENGUARD Gold Certified
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

Acoustical Performance
CAC testing conducted using Prelude® XL® suspension system.

Primary (Embodied) Energy
See all LCA information on our EPDs.

High Recycled Content
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines. HRC items contain 15% or greater post-consumer recycled ceilings.

Insulation Value
R Factor – 2.2 (BTU units); R Factor – 0.39 (Watts units)

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS
UL.COM/GG UL 2818



Cleaning and Disinfecting
Cleaning and CDC recommended disinfecting options available on armstrongceilings.com/cleaning

30-Year Performance Guarantee & Warranty
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty

Weight; Square Feet/Carton
1420, 1425 – 1.05 lbs/SF; 24 SF/ctn
1910, 1910HRC, 1913, 1913HRCv – 1.08 lbs/SF; 48 SF/ctn
1991 – 1.08 lbs/SF; 30 SF/ctn
1992 – 1.08 lbs/SF; 36 SF/ctn
1980 – 1.08 lbs/SF; 72 SF/ctn
1990 – 1.08 lbs/SF; 24 SF/ctn
1984 – 1.08 lbs/SF; 80 SF/ctn

Minimum Order Quantity
1 carton

Metric Items Available
1910M, 1913M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.



MINERAL FIBER – Standard

ULTIMA® ULTIMA® High NRC

Square Lay-in
fine texture



USDA
CERTIFIED
BIOBASED
PRODUCT
PRODUCT 95%

Declare.

SUSTAIN®
High Performance
Sustainable Ceiling Systems

GREENGUARD
Gold Certified
(details below)

LEED®
WELL™ | LBC

UP TO 87% RECYCLED CONTENT

- energy management
- construction waste mgmt
- regional materials
- design for flexibility
- EPD
- recyclable/producer resp.
- biobased materials
- recycled content
- sourcing of raw materials
- material ingredient reporting
- low emitting materials
- lighting quality
- acoustics

Calculate sustainability with GreenGenie™
armstrongceilings.com/greengenie

LOCATION DEPENDENT

VISUAL SELECTION

armstrongceilings.com/catdvwg	Susp. Dwg.	Item No.	Dimensions (Inches)
ULTIMA® with AirGuard™ Coating 15/16" Square Lay-in		1900	24 x 24 x 3/4" □
AirGuard™ Coating actively removes formaldehyde from indoor air.		1903	24 x 48 x 3/4" □

PERFORMANCE SELECTION

Dots represent high level of performance.

UL Classified Acoustics	Total Acoustics ¹	Articulation Class	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	CleanAssure™ Disinfectable Panels	DURABILITY	Recycle Program				
NRC + CAC =	NRC CAC							Fog	Wash	Impact	Scratch	Soil	Recycle Program	30-Yr Warranty
0.75 + 35 =	BETTER	N/A	Class A	0.88	•	•	•	•	•	•	•	•	•	•
0.75 + 35 =	BETTER	N/A	Class A	0.88	•	•	•	•	•	•	•	•	•	•

¹ Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product. **GOOD** (NRC 0.60-0.65; CAC 35+) **BETTER** (NRC 0.70-0.75; CAC 35+) **BEST** (NRC 0.80+; CAC 35+)

SUSPENSION SYSTEMS

15/16" **Blizzard White – Suspension System Finish**
A color and texture coordinated suspension system to complement Ultima® ceiling panels for a monolithic look and feel.

PHYSICAL DATA

Material
Wet-formed mineral fiber with DuraBrite® acoustically transparent membrane

Surface Finish
DuraBrite scrim with factory-applied latex paint

Fire Performance
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

ASTM E1264 Classification
Type IV, Form 2, Pattern E
Fire Class A

Humidity/Sag Resistance
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications.

Anti-Mold/Mildew
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

VOC Emissions
GREENGUARD Gold Certified
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

Acoustical Performance
CAC testing conducted using Prelude® XL® suspension system.

Primary (Embodied) Energy
See all LCA information on our EPDs.

High Recycled Content
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines. HRC items contain 15% or greater post-consumer recycled ceilings.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS
UL.COM/GG
UL 2818



Insulation Value
R Factor – 2.2 (BTU units); R Factor – 0.39 (Watts units)

Cleaning and Disinfecting
Cleaning and CDC recommended disinfecting options available on armstrongceilings.com/cleaning

30-Year Performance Guarantee & Warranty
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty

Weight; Square Feet/Carton
1900, 1903, – 1.08 lbs/SF; 48 SF/cartn

Minimum Order Quantity
1 carton



MINERAL FIBER – Standard