





Parts Breakdown

HM1317CB

Products with multiple versions are listed in subsiding order with the newest version on top not indented

<u>Fig #</u>	<u>Part ID</u>	<u>Part Name</u>	<u>Quantity</u>
1	266512-5	SET BOLT M10X142, HM1317CB	1
2	163506-0	SIDE HANDLE, HM1317CB	1
3	451331-4	HANDLE BASE, HM1317CB	1
5	252654-1	THUMB NUTM10, HM1317CB	1
6	253194-2	F. WASHER 5, HM1303B	1
7	922221-3	HEX BOLT M5X16, 6906	1
8	325895-3	TOOL RETAINER, HM1317CB	1
9	322477-2	TOOL RETAINER POLE, HM1500B	2
10	256219-1	PIN 4, HM1500	2
11	951272-9	SPRING PIN 8-40, HM1500B	2
12	324238-6	TOOL RETAINER SHAFT, HM1810	1
13	331872-5	TOOL HOLDER, HM1317CB	1
14	266011-7	HEX. SOCKET HEAD BOLT M8X35, HM1317CB	6
15	233083-7	COMP. SPRING 12, HM1800	2
16	322560-5	RETAINER RING, HM1800	2
17	213720-9	O RING 67, HR2400	1
18	262151-9	URETHAN RING 32, HM1317CB	1
19	257301-9	RING 35, HM1317CB	1
20	257788-5	SLEEVE 43, HM1317CB	1
21	213569-7	O RING 45, AN611	1
22	213192-8	X-RING 36, HM1317CB	1
23	213150-4	O-RING 36, HM1317CB	1
24	325687-0	IMPACT BOLT, HM1317CB	1
25	325683-8	WASHER 30, HM1317CB	1
26	424206-0	RUBBER RING 36, HM1317CB	1
27	325684-6	SHOULDER RING 32, HM1317CB	1
28	318458-2	BARREL, HM1317CB	1
29	325685-4	STRIKER, HM1317CB	1
30	213193-6	O-RING 42, HM1317CB	1
31	233977-6	RING SPRING 55, HM1317CB	1
32	331870-9	CYLINDER 52, HM1317CB	1
33	451168-9	SHOULDER SLEEVE, HM1317CB	1
34	234111-1	COMPRESSION SPRING 66, HM1317CB	1
35	265367-5	H.S.H.BOLT M8X40, HM1500	4
36	451169-7	WEIGHT GUIDE, HM1317CB	1
37	331867-8	COUNTER WEIGHT, HM1317CB	1
38	451169-7	WEIGHT GUIDE, HM1317CB	1
39	234111-1	COMPRESSION SPRING 66, HM1317CB	1
40	331868-6	SLIDE SLEEVE, HM1317CB	1
41	233977-6	RING SPRING 55, HM1317CB	1
42	213569-7	O RING 45, AN611	1
44	256238-7	PIN 12, HM1307CB	1
45	213193-6	O-RING 42, HM1317CB	1
46	318459-0	PISTON, HM1317CB	1
47	213569-7	O RING 45, AN611	1
48	451164-7	CONNECTING ROD, HM1317CB	1
49	268241-6	PIN 6, HM1317CB	1
50	213806-9	O RING 90, HM1500	1
51	318462-1	GEAR COVER, HM1317CB	1
52	266499-1	H.S. HEAD BOLT M6X30 W/GM, HM1307CB	6
53	227709-1	HELICAL GEAR 47, HM1317CB	1
54	211306-3	B. BEARING 6204LLB, HM1307CB	1
56	267166-1	FLAT WASHER, HM0860C	1
57	226156-3	GEAR CPL., HM1317CB	1
58	212159-3	NEEDLE CAGE 1412, HM1214C	1
59	262157-7	NYLON RING 14, HM1317CB	1
60	212159-3	NEEDLE CAGE 1412, HM1214C	1
61	267166-1	FLAT WASHER, HM0860C	1



Parts Breakdown

HM1317CB

62	424207-8	SEAL RING, HM1317CB	1
63	140056-2	CRNAK HOUSING CPL., HM1317CB	1
64	211373-8	BALL BEARING 6205LLU, HM1304B	1
65	331871-7	CRANK SHAFT, HM1317CB	1
66	331869-4	COUNTER SHAFT, HM1317CB	1
67	212264-6	NEEDLE ROLLER BEARING 1813, HM1317CB	1
68	325686-2	SHOULDER WASHER 8, HM1317CB	1
69	213809-3	O RING 87, HM1307CB	1
70	268240-8	PIN 10, HM1317CB	1
71	140057-0	BEARING BOX CPL., HM1317CB	1
72	961004-6	RETAINING RING S-8, LXP01	1
73	213261-5	O RING 17, AN451	1
74	265844-7	H.S.H BOLT M6X20, AN611	3
75	211032-4	B. BEARING 608ZZ, LXP01	1
76	962112-6	RETAINING RING R-22, AN451	1
77	443127-7	FILTER, HR4041C	1
78	213758-4	O RING 74, AN8300	1
79	451166-3	CRANK CAP COVER, HM1317CB	1
80	346546-5	PLATE, HM1214C	2
	941051-3	F. WASHER 4, LS1016L	
81	451167-1	REAR COVER, HM1317CB	1
82	266499-1	H.S. HEAD BOLT M6X30 W/GM, HM1307CB	6
83	331855-5	SEALING SCREW, HM1214C	1
84	211249-9	BALL BEARING 6302LLU, HM1214C	1
85	267397-2	FLAT WASHER 15, HM1307CB	1
86	240003-4	FAN 80, 5007F	1
87	517785-6	ARMATURE ASS'Y, HM1317CB	1
88	681642-5	INSULATION WASHER, LS1016L	1
89	210059-1	BALL BEARING 6000DDW, HR4040C	1
90	451107-9	WASHER GUIDE, HM1214C	1
91	267809-5	WAVE WASHER, HM1202C	1
92	451111-8	BAFFLE PLATE, HM1214C	1
93	266044-2	T. SCREW FLANGE 5X60, 5037NB	2
94	636331-7	FIELD, HM1317CB	1
95	451117-6	MOTOR HOUSING, HM1214C	1
96	638447-4	BRUSH HOLDER UNIT, HM1307CB	1
97	CB175	CARBON BRUSH SET, 195845-0	1
	CB171	CARBON BRUSH SET, 194990-8	
	195845-0	CARBON BRUSH SET, CB175	
	194990-8	CARBON BRUSH SET, 194990-8	
98	265995-6	TAPPING SCREW 4X18, BO4556K	4
99	158986-3	CONTROLLER COVER CPL., HM1214C	1
100	263027-3	RUBBER PIN 4, HM0860C	1
101	651423-1	SWITCH, HM1307CB	1
102	265995-6	TAPPING SCREW 4X18, BO4556K	2
103	687683-9	STRAIN RELIF, HM1317CB	1
104	265995-6	TAPPING SCREW 4X18, BO4556K	1
105	664290-5	CORD (2X14X16), HM1800	1
106	682578-1	CORD GUARD, HM1317CB	1
107	631919-8	CONTROLLER, HM1317CB	1
108	265490-6	HEX BOLT M4 X 16, 9560CV	2
109	232209-8	LEAF SPRING, HM0860C	1
110	451112-6	SLIDE LEVER, HM1214C	1
111	263027-3	RUBBER PIN 4, HM0860C	2
112	451105-3	LENS, HM1214C	1
113	451118-4	HANDLE, HM1214C	1
114	265995-6	TAPPING SCREW 4X18, BO4556K	1
115	451106-1	SWITCH LEVER, HM1214C	1
116	265995-6	TAPPING SCREW 4X18, BO4556K	1
117	266499-1	H.S. HEAD BOLT M6X30 W/GM, HM1307CB	4
118	867310-6	NAME PLATE, HM1317CB	1



Parts Breakdown

HM1317CB

119	451119-2	HANDLE COVER, HM1214C	1
120	265995-6	TAPPING SCREW 4X18, BO4556K	2
	442180-0	BOTH SIDE ADHESIVE TAPE, HM1214C	1
	141799-9	N/A	1
	126091-4	CONTROLLER ASS'Y, HM1317CB	
	D-21353	BULL POINT (1-1/8 HEX), HM1810	1
	D-31930	BULL POINT 520 BULK, HM1317CB	
	824897-1	PLASTIC TOOL CASE, HM1317CB	1
	809557-6	PLASTIC CASE LABEL, HM1317CB	2