



Eco-Surge 7-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Individually-Controlled

MODEL NUMBER: TLP76MSG



Highlights

- Individual outlet control
- 1080 joules
- 7 outlet / 6-ft cord
- Diagnostic LEDs

Package Includes

- TLP76MSG ECO-SURGE Home/Business Theater Surge Suppressor
- Instruction manual with warranty information

Description

Tripp Lite's TLP76MSG offers reliable, GREEN surge technology that protects your computer and peripherals as well as the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. The TLP76MSG has one always on outlet for those peripherals that need constant power like a fax machine, DVR or router. It also offer convenient, individual outlet switches that allow users to select which device is turned on and off. The TLP76MSG has 7 total outlets, 6 foot cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Designed with an attractive cool gray suppressor housing, the TLP76MSG can accommodate up to 4 transformer plug outlets offering convenient protection of desktop computer equipment and accessories. \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Energy-saving green outlets allow individual outlet control using illuminated power switches for cutting power to peripherals not in use.
- Six green outlets have their own illuminated ON/OFF switch for cutting power to peripherals when they are not in use. One "Always On" outlet provides continuous power for devices such as DVRs (TiVo), cable and satellite boxes, modems, routers and fax machines.
- In addition to the individual illuminated outlet switches, an illuminated Master Switch controls power to all outlets (except the Always On outlet) at once. It can override other "ON" settings to cut power to all switched outlets at once.
- Protected (Green) LED assures protection is present & Always On (Red) LED indicates that the Always On outlet is receiving power.
- 1080 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans).



- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332166074
OUTPUT	
Output Volt Amp Capacity (VA)	120
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Transformer Accommodation	(4) Yes
Right-Angle Outlets	Yes
Individually Controllable Load Banks	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	1 x Lighted Master Switch & 6 x Lighted Receptacle Switches
LED Indicators	Protected (Green)" & Always On Receptacle (Red)
SURGE / NOISE SUPPRESSION	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression.
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400v
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Anti-Microbial Protected	No
Color	Gray
Color (AC Line Cord)	Gray
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	Gray
Shipping Dimensions (hwd / cm)	5.08 x 10.67 x 43.18
Shipping Dimensions (hwd / in.)	2.00 x 4.20 x 17.00
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / cm)	3.56 x 8.64 x 38.1
Unit Dimensions (hwd / in.)	1.40 x 3.40 x 15
Unit Weight (kg)	0.70
Unit Weight (lbs.)	1.54
SPECIAL FEATURES	
Rotatable Outlets	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
Canada	cUL



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>