

3M Science.
Applied to Life.™



Get in the red zone

with strong, visible outdoor masking tapes.

3M™ Red Masking Tapes

Our high-strength, high-visibility red masking tapes securely seal most surfaces and hold strong in the most challenging conditions to help drive your projects into the red zone.



Experience the strength of red.

All of our 3M red masking tapes are designed to stick immediately, provide a strong weather-resistant seal and conform to irregular surfaces without lifting.



3M™ Outdoor Construction and Seaming Tape 5902



High-visibility performance.

- Designed for seaming poly with a tight seal prior to pouring cement
- Economical high tack
- Easy to tear off the roll by hand

3M™ Outdoor Masking Poly Tape 5903



Rugged outdoor performance.

- Designed for stucco and coated surfaces
- Ideal for outdoor holding, patching, bundling and marking
- Easy to tear off the roll by hand
- UV and weather-resistant: **30 day clean removal**

3M™ Outdoor Masking and Stucco Tape 5959



Superior strength, longest lasting performance.

- Designed for stucco, EIFS and other heavy coatings
- Superior tensile strength holds for up to one year
- Extended UV and weather-resistant: **3 month clean removal**
- Versatile indoor/outdoor protection

Product	Tape Structure (Backing/Adhesive)	Thickness mils (mm)	Adhesion to Steel oz/in (N/100 mm)	Tensile Strength lb/in (N/100 mm)	Elongation at Break %	Heat Resistance °F (°C)	Meets Specifications
Based on ASTM Test Method:		D-3652	D-3330	D-3759	D-3759		
3M™ Red Masking Tape							
5902	Polyethylene/Synthetic Rubber	8.4 (0.21)	68 (7.4)	16 (28)	300	—	—
5903	Polyethylene/Synthetic Rubber	7.5 (0.19)	79 (8.7)	21 (36.8)	72	173 (78) 30 Minutes	—
5959	Polyethylene Over Cloth Scrim/Rubber	12.0 (0.30)	53 (5.8)	35 (61.3)	16	200 (93) 30 Minutes	UL 723/ ASTM E84

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	3M UPC	Size	Rolls/Case
5903	00-051111-07591-3	5 in x 60 yd	8
	00-051115-31842-9	48 mm x 54.8 m	24

Product	3M UPC	Size	Rolls/Case
5902	00-689330-18960-1	48 mm x 54.8 m	24
5959	00-051115-25491-8	48 mm x 41.1 m	12



Closure and Masking Systems Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000

Phone 800-362-3550
Web 3M.com/Masking

For more information on 3M Masking Tapes, contact your local 3M representative or call 1-800-362-3550.

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted.

3M is a trademark of 3M. © 3M 2021. All rights reserved. Please recycle.