

Features

- Designed to meet food service standards
- Quick responding, high accuracy
- Large, easy-to-read backlit LCD display
- User selectable °C, °F
- Min/Max/Avg functions
- Relative mode and Data hold
- IP67 rated waterproof housing
- Low battery indicator and auto shut off
- Includes RTD temperature probe (PT-100), batteries

Specifications

Measuring Range:	-148 to 572°F (-100 to 300°C)
Accuracy:	±0.1% reading +0.8°F (+0.4°C)
Resolution:	0.1°F/°C
Type:	Single Input, RTD
Response Time:	2x/sec
Display:	3 1/2-digit LCD
Backlit Display:	Yes
Data Hold:	Yes
Min:	Yes
Max:	Yes
Average:	Yes
Relative Mode:	Yes
Auto Shut-off:	Yes (after 30 mins/off)
Low Battery Indicator:	Yes
Power Supply:	3 x AAA batteries
Battery Life:	Approx 100 hours (Alkaline)
Product Certifications:	IP67, CE
Operating Temperature:	32 to 104°F (0 to 40°C)
Storage Temperature:	14 to 140°F (-10 to 60°C)
Operating Humidity:	10-90%
Dimensions:	5.9 x 2.6 x 1.2" (150 x 66 x 31mm)
Weight:	6.2oz (175g)

TECHNICAL DATA



Model	Description
C-370	RTD Thermometer
TP-R01	Replacement RTD Temperature Probe
CA-05A	Soft Carrying Case
C-370-NIST	RTD Thermometer & NIST