



LF3600 Metal Push-to-Connect Fittings

To meet your technical and environment requirements, Legris' LF3600 fittings offers the robustness, reliability and resistance to industrial fluids for the most demanding environments.

Product Features:

- High phosphorous, FDA-compliant, chemical resistant, nickel-plated collet and body
- FKM seal
- Chemical, corrosion, and abrasion resistance
- NPT, BSPT, BSPP, and metric threads

Markets:

- Industrial
- Chemical
- Life Science
- Automation
- Food Processing

Applications:

- Food Fluids
- Harsh Detergents
- Cleaning In Cold/ Hot Water
- Steam
- Oils

Specifications:

Pressure Range	Up to 435 psi (30 bar)
Temperature Range	-4° to 302° F (-20° to 150° C)
Vacuum Capability	28" Hg

Note: Maximum working pressure and temperature are dependent on the type of tubing used

Note: Units with thread sealant do not meet FDA Compliance.

Compatible Tubing:

- Polyethylene
- Polyurethane 95 Durometer Shore A
- Nylon
- Fluoropolymer
- Stainless Steel (when grooved)
- Copper (when grooved)

Silicone-Free

