



The comprehensive range of Legris flow controls provide a solution for all flow regulation functions in a pneumatic system.

Select the model suited to your application according to:

5 Key Requirements

1.	Condition of Use	Standard applications	Glass reinforced Nylon 6.6 models
		Severe applications	Metal models
2.	Connection Options	On cylinder or threaded control valve	Models with NPT, BSPT, BSPP and Metric threads
		On cylinder or control valve with push-in connection	Plug-in models
3.	Dimensions	Standard applications require full flow rate performance and compact overall dimensions	Compact models
		Small diameter cylinders require precise and accurate adjustment and minimum size	Miniature models
4.	Type of Adjustment	Precise adjustment with locking nut ensuring the setting remains fixed	Models with external adjustment
		Precise adjustment with screwdriver and protection against unwanted adjustment	Models with recessed adjustment
5.	Installation Configuration	Standard applications	Banjo models
		Tube output that can be positioned through 180° and swivels with the tube movement	Models with swivel outlet
		Cylinder where access is difficult or where another function fitting is installed in the cylinder port	In-line models