

## NOT for Patient-Care Vicinity – UL 1363 Medical-Grade Power Strip with 6 Hospital-Grade Outlets, 6 ft. Cord

MODEL NUMBER: PS-606-HG



Medical-grade power strip with long 6 ft. cord provides versatile power distribution outside of patient-care vicinities.

### Description

The PS-606-HG Medical-Grade Power Strip supplies power outside of patient-care vicinities, such as administrative areas or in resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. Compliant with UL 1363 specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and six NEMA 5-15R-HG hospital-grade outlets.

Anti-Microbial Protected with EPA Registered and FDA Compliant Silver Ionic Technology known to inhibit growth of Microbes on surfaces.

A built-in resettable 15A circuit breaker controls power to all outlets and protects the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The 6 ft. cord reaches convenient power sources.

Keyhole mounting tabs and flanges make installing this power strip easy. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

### Features

**Power Distribution Outside of Patient-Care Vicinities** Ideal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes 120V, 50/60 Hz power strip complies with UL 1363 specifications

**Versatile Medical-Grade Solution** 6 NEMA 5-15R-HG hospital-grade outlets provide consistent power Rugged, all-metal housing for long life in demanding environments

**Premium Safety Features** Resettable 15A circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off

**Ready to Use Right Out of the Box** Built-in keyhole mounting tabs and flanges make the PS-606-HG easy to install on a variety of surfaces

**Exclusive, Patented Antimicrobial Protection** Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria like C. diff and MRSA Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

### Highlights

- Approved for use outside of patient-care vicinities
- Complies with UL 1363 specifications
- 6 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Features 6 NEMA 5-15R-HG hospital-grade outlets
- Easy to mount on a variety of surfaces
- Exclusive, patented anti-microbial coating - 99.9% effective in inhibiting bacteria and viruses

### Package Includes

- PS-606-HG UL 1363 Medical-Grade Power Strip with six 15A Hospital-Grade Outlets and 6 ft. Cord
- Owner's Manual



## Specifications

OVERVIEW	
UPC Code	037332121035
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Anti-Microbial Protected	Yes
Color	White
Color (AC Line Cord)	White
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Receptacle Color	White
Shipping Dimensions (hwd / cm)	6.10 x 14.73 x 36.07
Shipping Dimensions (hwd / in.)	2.40 x 5.80 x 14.20
Shipping Weight (kg)	1.18
Shipping Weight (lbs.)	2.60
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.09
Unit Weight (lbs.)	2.40
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
Canada	cUL (Series Number: AGIB12015SL)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>