



Main

| | |
|-------------------------------|---|
| Range of Product | Harmony Electromechanical Relays Harmony Timer Relays |
| Product or Component Type | Socket |
| Contact terminal arrangement | Mixed |
| Product compatibility | Plug-in relay RUM 2 C/O Plug-in relay RE48 2 C/O Plug-in relay RE48 1 C/O + 1 C/O |
| Shape of pin | Cylindrical |
| Device short name | RUZ |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|---|--|
| [Ith] conventional free air thermal current | 10 A |
| [Ue] rated operational voltage | < 250 V |
| Tightening torque | < 1 N.m M3.5 |
| Fixing mode | By screw panel) Clip-on 35 mm symmetrical DIN rail) |
| Marking | CE |
| Width | 1.50 in (38 mm) |
| Net Weight | 0.12 lb(US) (0.054 kg) |

Environment

| | |
|---------------------------------------|--|
| Connections - terminals | Connector, 1 x 0.25...1 x 2.5 mm ² AWG 22...AWG 14) flexible with cable end Connector, 2 x 0.25...2 x 1 mm ² AWG 22...AWG 17) flexible with cable end Connector, 1 x 0.5...1 x 2.5 mm ² AWG 20...AWG 14) solid without cable end Connector, 2 x 0.5...2 x 1.5 mm ² AWG 20...AWG 16) solid without cable end |
| Standards | IEC 61984 |
| Product Certifications | UL CSA |
| Ambient Air Temperature for Storage | -40...185 °F (-40...85 °C) |
| Ambient air temperature for operation | -40...131 °F (-40...55 °C) |
| IP degree of protection | IP20 conforming to EN/IEC 60529 |
| Dielectric strength | 2500 V |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21128 - ZELIO ICE CUBE RELAY ACCESSORIES |
| Discount Schedule | CP2 |
| GTIN | 3389119403214 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.01 lb(US) (0.005 kg) |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.33 in (8.4 mm) |
| Package 1 width | 0.34 in (8.6 mm) |
| Package 1 Length | 0.57 in (14.6 mm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 22.19 oz (629 g) |
| Package 2 Height | 3.31 in (8.4 cm) |
| Package 2 width | 3.39 in (8.6 cm) |
| Package 2 Length | 5.75 in (14.6 cm) |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 200 |
| Package 3 Weight | 27.73 lb(US) (12.58 kg) |
| Package 3 Height | 11.22 in (28.5 cm) |
| Package 3 width | 11.77 in (29.9 cm) |
| Package 3 Length | 15.67 in (39.8 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Socket

8-Pin Socket

