

AFTER REMOVING LENS ASSEMBLY:

For Lower Temperature: Place left index finger at left side of the wide end of pointer close to the hub. Insert screwdriver in pointer slot and turn slowly clockwise. Adjust to proper setting.

For High Temperature: Place left index finger at right side of the wide end of pointer close to the hub.

CAUTION

This unit is not waterproof. Do not immerse. If unit becomes wet inside, unstable readings may occur.

Panel Mount Thermometer

-40°F to 15°F / -40°C to 60°C



Front Flange/Back Connect

- 2" Dial (5.08 cm)
- 48" (121.9 cm) Capillary
- Sensor Dimension :2.5x 0.312(In)
- Recalibrate able
- Accuracy: +/- 2

