

Core & Coil (71A) HPS ~GT~ 400W

CORE & COIL HID HPS BAL 1000W S52 5-TAP KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S52
Lamp Type	1000W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A8753
Core Size	4 1/4 x 6
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI571-H5
Ignitor Temperature Rating	105°C
Capacitor Value	26 MFD
Capacitor Catalog Number	RW1626020
Capacitor Requirements	525V
Capacitor Temperature Rating	90°C
Capacitor Diameter/Oval	1.75 in
Dimensions	
Capacitor Height	4.25 in
Automatic Restart	No


Operating and Electrical	
Input Voltage	120/208/240/277/480 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	3.9/2.19/2.01/1.71/0.96 A
Input Current (Starting)	7.8/4.38/3.82/3.3/1.9 A
Input Current (Short Circuit)	5.83-8.74/3.36-5.05/2.92-4.38/2.53-3.8/1.46-2.19 A
Secondary Short Circuit Current	6.24-7.63 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	437 V
Input Current (Operating) (Nom)	9.28/5.32/4.68/4.03/2.31 A A
Input Power (Nom)	1100 W
Rated Lamp Watts	1000 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) HPS ~GT~ 400W

Max Ballast-Lamp Distance	15'
Remote Wiring	
Recommended Fuse Value	25/15/12/10/6 A
Approval and Application	
Open Circuit Voltage Test (Volts)	390-476 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/C/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029C
Product Data	
Order product name	CORE & COIL HID HPS BAL 1000W S52 5-TAP KIT
EAN/UPC - Product	781087111826
Order code	71A8753001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710405501
Net Weight (Piece)	13.903 kg

Dimensional drawing



HPS BAL 1000W S52 5-TAP KIT

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID HPS BAL 1000W S52 5-TAP KIT	6 in	3.97 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

