

Product data sheet

Characteristics

2510KS2

Switch, manual, 30A, 3 pole, 10 HP at 575 VAC, three phase, toggle operated, no indicator, NEMA 1 stainless steel flush



Main

Product	Single Unit Manual Switch
Type	K

Complementary

Current Rating	30 A
Horsepower Rating	2 Hp 115 V AC 1 Hp 90 V DC 2 Hp 115 V DC 1.5 Hp 230 V DC 7.5 Hp 230 V AC 10 Hp 460 V AC 10 hp 575 V AC
Maximum Voltage Rating	600 V AC 230 V DC
Number of Poles	3P
Control Unit Type	Toggle
Number of Phases	3 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.5 in (114.30 mm)
Width	2.75 in (69.85 mm)
Depth	2.5 in (63.50 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA Enclosure Rating	Not rated (flush plate) Stainless Steel standard size

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	785901554684
Nbr. of units in pkg.	1
Package weight(Lbs)	8.16 oz (231.332 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.10 in (5.334 cm)
Package 1 width	3.00 in (7.62 cm)
Package 1 Length	4.70 in (11.938 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------