

# 2510MCG3

Manual Starter, integral horsepower, NEMA M1, 600 VAC, 3 pole, 10 HP at 380/575 VAC, three phase, no indicator, NEMA 1



## Main

Product	Manual Starter
Type	M
NEMA Size	M-1

## Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	7.5 Hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	8.63 in (219.20 mm)
Width	5 in (127.00 mm)
Depth	4.13 in (104.90 mm)
Net Weight	4.21 lb(US) (1.91 kg)

## Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
NEMA Enclosure Rating	NEMA 1 painted sheet steel

## Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	785901792109
Nbr. of units in pkg.	1
Package weight(Lbs)	4.20 lb(US) (1.905 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.50 in (11.43 cm)
Package 1 width	5.70 in (14.478 cm)
Package 1 Length	9.20 in (23.368 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	126
Package 2 Weight	536.00 lb(US) (243.125 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

