

# Product data sheet

## Characteristics

# 8538SBA23V02S

NEMA Combination Starter, Type S, 30A  
fusible disconnect, Size 0, 18A, 5 HP at 600  
VAC polyphase, 120 VAC coil, NEMA 12



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	5 Hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
NEMA size	0

### Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

### Ordering and shipping details

Category	21212-8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	785901743965
Nbr. of units in pkg.	1
Package weight(Lbs)	37.54 lb(US) (17.028 kg)
Returnability	No
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.00 in (27.94 cm)
Package 1 width	12.80 in (32.512 cm)
Package 1 Length	28.80 in (73.152 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------