


Penal-Ware[®] 1675 Series

Blowout Jet Toilet - Off-Floor



Blowout Jet Toilet - Off-Floor

Fixture is arranged to be installed on finished wall and serviced from an accessible pipe chase. Optional Wall Sleeve or Metal Template is recommended for all installations for required wall openings. Toilet bowl is fabricated from 14 gage, type 304 stainless steel and is seamless welded construction. Wall flange is structurally reinforced. Exterior is polished to a satin finish. The inside of the toilet bowl also has a satin finish. There are no accessible voids or crevices where contraband can be concealed.

Toilet is a blowout jet type with an elongated bowl manufactured to ASME A112.19.3 and CSA B45.4 requirements and will flush with a minimum of 25 PSI flow pressure when used in conjunction with a minimum of 1.28 GPF. Trap has a minimum 3-1/2" seal and will pass a 2-1/8" ball. Toilet waste outlet is 2-3/8" diameter plain end extending 3" beyond the back of the unit.

Regularly Furnished items include mounting hardware.

GUIDE SPECIFICATION

Provide and install Acorn Penal-Ware Blowout Jet Toilet (specify model number and options). Toilet bowl shall be fabricated from 14 gage, type 304 stainless steel. Construction shall be seamless welded and exposed surfaces shall have a satin finish. Toilet shall be concealed blowout jet type with an elongated bowl, a self-draining flushing rim, and an integral contoured seat. Toilet shall meet ASME A112.19.3 and CSA B45.4 requirements and will flush with a minimum of 25 PSI flow pressure when used in conjunction with a minimum of 1.28 GPF. Toilet trap shall have a minimum 3-1/2" seal that shall pass a 2-1/8" diameter ball and be fully enclosed. Fixture shall withstand loadings of 3,000 pounds without permanent damage. Fixture shall be furnished with necessary fasteners for proper installation.

Page 1 P.1675

Revised: 03/15/19

Penal-Ware® 1675: Blowout Jet Toilet - Off-Floor

WALL THICKNESS AND TYPE (Must Specify)

_ Type: 🗋 Concrete 🗋 Block 🗋 Steel Thickness:

MODEL NUMBER AND OPTIONS SELECTION:

BASE MODEL NUMBER

Blowout Jet Toilet **1**675

SUPPLY (Must Specify)

🗆 -Т Top (Exposed) 🗆 -W Wall (Concealed)

FIXTURE MOUNTING AND WASTE (Must Specify)

Off-Floor, Wall Outlet M-1

FLUSH VALVE GPFs (Must Specify)

-1.28 GPF (HET)

-1.6 GPF (Not Available in California)

-3.5 GPF (Not Available in California)

FLUSH VALVE OPTIONS (Must Specify) ***REFER TO ACORN DURA-WARE ACCESSORIES FOR FLUSH** VALVE COVER #2802, BOX #2803-1 AND PANEL #2898*

- Master-Trol[®] Electronic Flush Valve (N/A for Top -EVSFV Supply)
- □ -EVSPFV Master-Trol® Electronic Flush Valve w/ Piezo Button (N/A for Top Supply)
- 🗋 -FV Flush Valve, Mechanical (N/A for ADA)
- -FVBO Flush Valve by Others
- 🗋 -FVH Flush Valve, Hydraulic (N/A for Top Supply)
- -FVL Flush Valve, Lever Handle (Wall Supply)
- -MTPFV Master-Trol® PLUS Electronic Flush Valve (N/A for Top Supply)
- -MTPPFV Master-Trol® PLUS Electronic Flush Valve w/ Piezo Button (N/A for Top Supply)
- -MVCFV Time-Trol® Electronic Flush Valve (N/A for Top Supply)

TOILET SEAT OPTIONS

- -HPS High Polish Integral Seat
- -HS Hinged Seat (N/A with #2802 Flush Valve Cover)
- -PFS Punched for Seat by Others


TOILET OPTIONS

- Cleanout w/ O-Ring Connecting to No-Hub 4" 🗆 -CO1 (Plain End Only)
- 🗋 -CO1-3 Cleanout w/ O-Ring Connecting to No-Hub 3" (Plain End Only, N/A with -WO3)
- -COH Cleanout Hook Assembly
- Flood-Trol (N/A w/ Top Supply) 🗋 -FT
- 🗆 -FTA Flood-Trol Auto-Reset (N/A w/ Top Supply)
- Flood-Trol Electronic 🗋 -FTE
- -FVT Flush Thru Wall Connector
- 🗋 -GW Gasketed Toilet Waste
- -PC Pinned Cleanout Plug (For -CO1 Options above)
- -TSC Toilet Shipping Cover
- Toilet Waste Extension (3" Standard) -TWE
 - Specify Length Beyond Fixture:
- 3" Bell Waste Outlet w/ Std. 2-3/8" Trap 🗋 -WO3B

PRODUCT OPTIONS


- 18" Integral Seat Height 🗋 -ADA 🗋 -EG Enviro-Glaze Color Specify:_ Toilet Interior & Exterior 🗋 -EGE Enviro-Glaze Color Specify:_
- Toilet Exterior Only Metal Template (Only 1 Required Per Project) 🗋 -MT
- -SW Wall Sleeve
- 🗋 -TF Transformer, 120VAC to 24VAC (-MVCFV option)
- -VAC AcornVac System

Please visit www.acorneng.com for most current specifications.



NOTES: 1.

- Optional -FV Flush Valve - Wall Supply
- Optional -FV Flush Valve - Top Supply
- **Toilet Waste Outlet** 3.
- 4. Wall Mounting Hardware



WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov Λ

Important: Installation instructions and current rough-in are furnished with each insture. Do not rough in without certified dimensions. Dimensions are subject to manufacturer's tolerance of plus or minus 1/4" and change without notice. Acom assumes no responsibility for use of void or superseded data. © Copyright 2009 Acom Engineering Company	
Selection Summary	Approved for Manufacturing
Model No. & Option	CompanyTitle
Quantity	Signature Date
Page 2 P.1675 Revised: 03/15/19	

Acorn Engineering Company • 15125 Proctor Avenue • P.O. Box 3527 • City of Industry, CA 91744-0527 U.S.A. Tel: (800) 488-8999 • (626) 336-4561 • Fax: (626) 961-2200 • www.acorneng.com • E-mail: info@acorneng.com