

Penal-Ware® 1418 Series

18" Lav-Toilet Comby with Lavatory Oval Bowl





1418-CT-2-BP-04-FV-PHLF

1418-AL-2-BP-04-FV-PHC

Fixture May Show Some Available Options

Please visit www.acorneng.com for most current specifications.

18" Lav-Toilet Comby with Lavatory Oval Bowl

Fixture is arranged to be installed on finished wall and serviced from an accessible pipe chase. Optional Wall Sleeve or Metal Template is recommended for all installations for required wall openings. Fixture is fabricated from 14 gage, type 304 stainless steel cabinet and toilet bowl and is seamless welded construction with a satin finish. The inside of the toilet bowl also has a satin finish. Cabinet interior is sound-deadened with fire-resistant material. There are no accessible voids or crevices where contraband can be concealed.

Lavatory Oval Bowl is 14-3/4" x 9-1/2" x 5" deep. Standard elbow waste outlet is 1-1/2" O.D. plain end.

Optional Valve may be an Air-Control pneumatically operated, pushbutton valve using atmospheric air. Pushbutton is vandal-resistant and requires less than 5 pounds to activate valve. Valve is direct acting, non-metering type and is optionally available as metering with non-hold open feature. Metering valve timing is adjustable from 5 to 60 seconds. Valve includes a 0.5 GPM flow control and can be remotely located up to 10 feet from the operating pushbutton. Valve and bubbler conform with lead free requirements of NSF61, Section 9 and CHSC 116875.

Toilet is blowout jet type with elongated bowl manufactured to ASME A112.19.3 and CSA B45.4 requirements and will flush with a minimum of 25 PSI flow pressure when used in conjunction with a minimum of 1.28 GPF. Trap has a minimum 3-1/2" seal and will pass a 2-1/8" ball. Toilet waste outlet is 2-3/8" diameter plain end extending 3" beyond the fixture for wall outlet or Gasketed Waste for floor outlet.

Regularly Furnished items include a fast drain, an integral self-draining soap dish, and mounting hardware.

GUIDE SPECIFICATION

Provide and install Acorn Penal-Ware 18" wide Lav-Toilet Comby (specify model number and options). Fixture shall be fabricated from type 304 stainless steel. Construction shall be seamless welded and exposed surfaces shall have a satin finish. Countertop shall have an air-circulating, self-draining soap dish. Provide Air-Control pneumatically operated pushbutton valve. Valve and bubbler conform with lead free requirements of NSF61, Section 9 and CHSC 116875. Toilet shall be concealed blowout jet type with an elongated bowl, a self-draining flushing rim, and an integral contoured seat. Toilet shall meet ASME A112.19.3 and CSA B45.4 requirements and will flush with a minimum of 25 PSI flow pressure when used in conjunction with a minimum of 1.28 GPF. Toilet trap shall have a minimum 3-1/2" seal that shall pass a 2-1/8" diameter ball and be fully enclosed. Cabinet interior is sound-deadened with fire-resistant material. Fixture shall withstand loadings of 5,000 pounds without permanent damage. Fixture shall be furnished with necessary fasteners for proper installation.


> Page 1 P.1418 Revised: 03/15/19

Penal-Ware® 1418: 18" Lav-Toilet Comby with Lavatory Oval Bowl



NOTES:

- 1. -04 Hot & Cold Air-Control Valve Shown
- 2. Lavy Valve Pushbuttons
- 3. Lavy -BP Penal Bubbler Shown
- 4. Optional -FV Flush Valve Shown
- 5. Lavy Waste Outlet
- 6. Toilet Waste Outlet
- 7. Wall Mounting Hardware





Penal-Ware® 1418: 18" Lav-Toilet Comby with Lavatory Oval Bowl

WALL THICKNESS AND TYPE (Must Specify) Thickness: Type: _ Concrete _ Block _ Steel			FLUSH VALVE GPF's (Must Specify) -1.28 GPF (HET) -1.6 GPF (Not Available in California)		
MODEL AND OPTIONS SELECTION:			☐ -1.6 GPF (Not Available in California) ☐ -3.5 GPF (Not Available in California)		
BASE MODEL NUMBER ✓ 1418 18" Lav-Toilet Comby			FLUSH VALVE OPTIONS (Must Specify)		
☐ -AL ☐ -AR ☐ -CT	NTATION (Must Specify) Angled Left Angled Right Centered Toilet		□ -EVSPFV□ -FV□ -FVBO□ -FVH	Master-Trol® Electronic Flush Valve w/ Piezo Button Flush Valve, Mechanical Flush Valve by Others Flush Valve, Hydraulic	
FIXTURE MO ☐ -1 ☐ -2	UNTING AND WASTE (Must Specify) Off-Floor, Wall Outlet On-Floor, Wall Outlet		_	Master-Trol® PLUS Electronic Flush Valve w/ Piezo Button	
<u> </u>	On-Floor, Floor Outlet		-MVCFV	Time-Trol® Electronic Flush Valve	
BUBBLER SELECTION (Must Specify)			CABINET OPTIONS ☐ -FMT Fixture Mounted Trim		
☐ -BC ☐ -BP	Bubbler, Code Bubbler, Penal		-FMI	Integral Shelf	
☐ -BPH	Bubbler, Penal Hemispherical		□ -PH	Paper Holder L R C LF RF	
LF	Lav-Filler		☐ -TB ☐ -TG	Toothbrush Holder ☐ Left ☐ Right 12 Gage Cabinet	
VALVE SELECTION (Must Specify) Air-Control (Pneumatic)			☐ -TH	Towel Hook ☐ Single ☐ Double ☐ Left ☐ Right	
□ -03	Single Temp, Non-Metering		☐ -VG1 ☐ -VG2	Vent Grille, 5-3/4" x 8-3/4" ☐ L ☐ R ☐ LF ☐ RF Vent Grille, 8-3/4" x 13" (Bottom Only)(-1 Only)	
☐ -03-M	Single Temp, Metering		_		
☐ -04 ☐ -04-M	Hot & Cold, Non-Metering Hot & Cold, Metering		-CW	Y WASTE OPTIONS Combined Waste	
☐ -04-MH	Hot & Cold, Metering Hot Side Only		LW1	Lavy Thru-Wall Extension with P-Trap	
Master-Trol®	(Electronic)		🔲 -LWE	Lavy Waste Extension (3" Standard)	
-EVS1	Single Temp		☐ -OF	Specify Length Beyond Fixture: Lavatory Overflow	
-EVS2	Hot & Cold		-PT	1-1/2" Removable P-Trap Waste	
☐ -EVSP1 ☐ -EVSP2	Single Temp, Piezo Button Hot & Cold, Piezo Buttons		TOILET OF	PTIONS	
_	PLUS (Electronic)		☐ -CO1	Cleanout w/ 2-3/8" OD O-Ring Connection to No-Hub	
-MTP1	Single Temp			4" (Plain End Only, Not Applicable with GW or -3 Floor Outlet)	
☐ -MTP2	Hot & Cold		☐ -CO1-3	Cleanout w/ 2-3/8" OD O-Ring Connection to No-Hub	
☐ -MTPP1 ☐ -MTPP2	Single Temp, Piezo Button Hot & Cold, Piezo Buttons			3" (Plain End Only, Not Applicable with GW or -3 Floor	
_	/E OPTION		🔲 -СОН	Outlet) Cleanout Hook Assembly	
🔲 -PFB	Power Failure Bypass (Provides drinking water		-FT	Flood-Trol	
	in the event of power failure)		☐ -FTA ☐ -FTE	Flood-Trol, Auto-Reset Flood-Trol, Electronic	
Time-Trol® (I	Electronic) Single Temp		-FVO	Flush Valve Opposite In Lieu of Standard Location	
	Single Temp Battery Powered		-FVT	Flush Valve Thru Wall Connector	
	(Batteries Not Included)		☐ -GW ☐ -HPS	Gasketed Toilet Waste (Wall Outlet) High Polish Seat #7 Finish	
☐ -MVC2 ☐ -MVC2-BAT	Hot & Cold Hot & Cold Battery Powered		-HS	Hinged Seat	
- TIVEZ B/(I	(Batteries Not Included)		☐ -PC	Pinned Cleanout Plug (For -CO1 Options above)	
Programmab	le (Electronic) w/9VDC Plug-In Transformer		☐ -SPS ☐ -TSC	Ligature Resistant Skirt Toilet Shipping Cover	
-PPZ1	Single Temp Programmable Piezo Button		TWE	Toilet Waste Extension (3" Standard)	
☐ -PPZ2	Hot & Cold Programmable Piezo Button		□ WO2B	Specify Length Beyond Fixture:	
Valve By Others ☐ -9 Punched for Valve by Others			☐ -WO3B	2-3/8" P-Trap w/ 3" Plain End Waste Outlet	
			PRODUCT ☐ -EG	Enviro-Glaze Color Specify:	
VALVE OPTIC ☐ -BRS	Brass Body Valve			Toilet Interior & Exterior	
-CI	Cycle Interrupt for Time-Trol® Valves		☐ -EGE	Enviro-Glaze Color Specify:	
☐ -MA2	Manifolded, 2-Stack		☐ -LPFV	Toilet Exterior Only Less Punching for Flush Valve	
☐ -MA3☐ -MA4	Manifolded, 3-Stack (N/A with -PFB option) Manifolded, 4-Stack (N/A with -PFB option)		☐ -MT	Metal Template (Only 1 Required Per Project)	
-PBH	Hemispherical Pushbutton		SW	Wall Sleeve AcornVac System	
☐ -PBP ☐ -TF	Pushrod Activated Pushbutton Transformer, 120VAC to 24VAC (-MVC option		☐ -VAC	Acomitac System	
□ -1F	only)				
Please visit www.acorneng.com for most current specifications. WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov					
Important: Installation instructions and current rough-in are furnished with each fixture. Do not rough in without certified dimensions. Dimensions are subject to manufacturer's tolerance of plus or minus 1/4" and change without notice. Acom assumes no responsibility for use of void or superseded data. © Copyright 2009 Acorn Engineering Company					
Selection Summary Approved for Manufacturing					
Model No. & Option Title					
Quantity			Signatur	e Date	

Tel: (800) 488-8999 • (626) 336-4561 • Fax: (626) 961-2200 • www.acorneng.com • E-mail: info@acorneng.com