



Example: T25F-C16



COLOR AVAILABILITY

COLOR	COLOR SUFFIX	MATERIAL							
		POLYETHYLENE	WEATHER RESISTANT POLYETHYLENE	FLAME RETARDANT POLYETHYLENE V2 RATING	FLAME RETARDANT POLYETHYLENE V0 RATING	FLAME RETARDANT HALOGEN FREE NYLON V0 RATING	NYLON	WEATHER RESISTANT NYLON	TEFLON
NATURAL (CLEAR)	LEAVE BLANK	X		NATURAL COLOR IS WHITE	NATURAL COLOR IS WHITE		X		X
WEATHER RESISTANT BLACK	0		X					X	
BLACK	20			X	X	X			
BROWN	1	X							
RED	2								
ORANGE	3	X							
YELLOW	4	X							
GREEN	5	X							
BLUE	6	X							
PURPLE	7	X							
GRAY	8	X							
WHITE	10	X							
PINK	16	X							



- Notes:
1. Refer to Panduit Catalogs for any additional information.
 2. For roll sizes larger than 10 ft., splicing may occur. For additional information, contact Tech.Support at 1-800-777-3300.
 3. Refer to Panduit Catalogs for dimensional data.
 4. Colors are stocked for 1/4" and 1/2" Polyethylene. Other sizes available, consult factory.

CAD FILENAME/LAYERS G00239HA_DC_SPIRALWRP_01

PANDUIT CORP. TINLEY PARK, ILLINOIS

SPIRAL WRAP (CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) .XXX
 (.XX) ANGLES

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

I	5-23-13	LEF	VJS	A. ADDED NZFR TO MATRIX B. UPDATED NOTE #2 C. ADDED "CUSTOMER DRAWING" TO TITLE BLK D. REPLACED TOLERANCES IN THE TITLE BLK WITH --	GB0239HA	I	RAMI		
R	12-4-00	JAD		INITIAL RELEASE	GB0239HA	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

DRAWN BY	JAD	MAT'L:		SCALE	NONE
DATE	12-4-00		SEE TABLE	DRAWING NO.	GB0239HA
CHK'D				DWG SIZE	A