



## Adjustable Wrench Specification Table

Grainger SKU	MFG Model#	Size (Inch)	Overall Length (Inch)		Full Opening of Jaw Not Less Than Inches	Hardness (HRC)		Proof Torque (In LBS)
			Min	Max		Movable Jaw	Handle	
1NYA1	WB27-4	4	3.5	4.5	1/2	40-50	40-50	600
1NYA2	WB27-6	6	5.5	6.5	15/16	40-50	40-50	1,450
1NYA3	WB27-8	8	7.5	8.5	1 1/8	40-50	40-50	2,700
1NYA4	WB27-10	10	9.5	10.5	1 5/16	40-50	40-50	4,500
1NYA5	WB27-12	12	11.5	12.5	1 1/2	40-50	40-50	7,650
1NYA6	WB02-15	15	14.5	15.5	1 11/16	40-50	40-50	15,000
1NYA7	WB02-18	18	17.5	19	2 1/16	40-50	40-50	20,000
1NYA8	WB02-24	24	23.5	25	2 7/16	40-50	40-50	20,000
1NYA9	WB27-B4	4	3.5	4.5	1/2	40-50	40-50	600
1NYB1	WB27-B6	6	5.5	6.5	15/16	40-50	40-50	1,450
1NYB2	WB27-B8	8	7.5	8.5	1 1/8	40-50	40-50	2,700
1NYB3	WB27-B10	10	9.5	10.5	1 5/16	40-50	40-50	4,500
1NYB4	WB27-B12	12	11.5	12.5	1 1/2	40-50	40-50	7,650
1NYB5	WB02-B15	15	14.5	15.5	1 11/16	40-50	40-50	15,000
1NYB6	WB02-B18	18	17.5	19	2 1/16	40-50	40-50	20,000
1NYB7	WB02-B24	24	23.5	25	2 7/16	40-50	40-50	20,000
1NYB8	WB27-6810	6, 8, 10	N/A	N/A	N/A	40-50	40-50	N/A
1NYB9	WB27-B6810	6, 8, 10	N/A	N/A	N/A	40-50	40-50	N/A
1NYC1	WB27-C4	4	3.5	4.5	1/2	40-50	40-50	600
1NYC2	WB27-C6	6	5.5	6.5	15/16	40-50	40-50	1,450
1NYC3	WB27-C8	8	7.5	8.5	1 2/16	40-50	40-50	2,700
1NYC4	WB27-C10	10	9.5	10.5	1 5/16	40-50	40-50	4,500
1NYC5	WB27-C12	12	11.5	12.5	1 1/2	40-50	40-50	7,650
1NYC6	WB02-C15	15	14.5	15.5	1 11/16	40-50	40-50	15,000
1NYC7	WB25-6	6	5.5	6.5	15/16	40-50	40-50	1,450
1NYC8	WB25-8	8	7.5	8.5	1 2/16	40-50	40-50	2,700



## Adjustable Wrench Specification Table

Grainger Sku	MFG Model#	Size (Inch)	Overall Length (Inch)		Full Opening of Jaw Not Less Than Inches	Hardness (HRC)		Proof Torque (In LBS)
			Min	Max		Movable Jaw	Handle	
1NYC9	WB25-10	10	9.5	10.5	1 5/16	40-50	40-50	4,500
1NYD1	WB25-12	12	11.5	12.5	1 1/2	40-50	40-50	7,650
1NYD2	WB27-C6810	6, 8, 10	N/A	N/A	N/A	40-50	40-50	N/A
1NYD3	WB27-C810	8, 10	N/A	N/A	N/A	40-50	40-50	N/A
1NYD4	WB27-C46	4, 6	N/A	N/A	N/A	40-50	40-50	N/A
1NYD5	PRO-ASW06	6	5.65	6 1/2	15/16	40-50	40-50	1,475
1NYD6	PRO-ASW08	8	7.6	8 1/2	1 1/8	40-50	40-50	2850
1NYD7	PRO-ASW10	10	9.5	10 8/16	1 5/16	40-50	40-50	4600
1NYD8	PRO-ASW12	12	11.5	12 1/2	1 1/2	40-50	40-50	7850

*NOTE: All Westward Adjustable Wrenches have the same footprint.*