



ELEMENT SPECS		
PART NUMBER	32-02	
MATERIAL	PAPER	
FLOW RATE	175 CFM	297 m <sup>3</sup> /hr
SURFACE AREA	2.0 ft <sup>2</sup>	0.2 m <sup>2</sup>
I.D.	4.25"	108mm
O.D.	6.00"	152mm
HEIGHT	2.50"	64mm