HBL[®] Extra Heavy Duty Industrial Series, 15A. 120/277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Black Brown Gray	HBL1201BK HBL1201 HBL1201GY HBL1201I	– HBL1202 – HBL1202I	HBL1203BK HBL1203 HBL1203GY	HBL1204BK HBL1204 HBL1204GY
	lvory Light Almond Red	HBL1201LA HBL1201LA HBL1201R	HBL12021 — —	HBL1203I — —	HBL1204I — —
	White	HBL1201W	_	HBL1203W	HBL1204W

20A, 120/277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Black Brown Gray Ivory Light Almond Red White	HBL1221BK HBL1221 HBL1221GY HBL1221I HBL1221LA HBL1221R HBL1221W	HBL1222BK HBL1222 HBL1222GY HBL1222I HBL1222LA HBL1222R HBL1222W	HBL1223BK HBL1223 HBL1223GY HBL1223I HBL1223LA HBL1223R HBL1223W	HBL1224BK HBL1224 HBL1224GY HBL1224I HBL1224LA HBL1224R HBL1224W
30A, 120/27	7V AC				
Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle.	Brown Ivory White	HBL3031 HBL3031I —	HBL3032 HBL3032I HBL3032W	HBL3033 HBL3033I —	

HBL[®] Extra Heavy Duty Industrial Locking Series, 15A. 120/277V AC

104, 120/21					
Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Key Guide, back and side wired.	Black Gray Ivory White	HBL1201L HBL1201LG HBL1201LI HBL1201LW	HBL1202L HBL1202LG HBL1202LI HBL1202LW	HBL1203L HBL1203LG HBL1203LI HBL1203LW	HBL1204L HBL1204LG HBL1204LI HBL1204LW
Key for Locking	g switch.	HBL1209			

20A, 120/277V AC


Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Key Guide, back and side wired.	Black Gray Ivory White	HBL1221L HBL1221LG HBL1221LI HBL1221LW	HBL1222L HBL1222LG HBL1222LI HBL1222LW	HBL1223L HBL1223LG HBL1223LI HBL1223LW	HBL1224L HBL1224LG HBL1224LI HBL1224LW
Key for Locking switch.		HBL1209			

$\rm HBL^{\circledast}$ Extra Heavy Duty Industrial AC Barrel Key Locking Switch^+, 20A, 120/277V AC

Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Chrome operator, back and side wired	Chrome	HBL1221RKL*	HBL1222RKL*	HBL1223RKL*	HBL1224RKL*
Replacement Barrel Key. HBL1209RKL					
See page D-15	section, page O-17	for locking switch w page D-16 for wallp	allplates.		

HP Conversion Chart

	001110101011	on an e		
	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP



(L) (L)

FULS

#6-32 - TAP

> 2.28" (57.9)

1.13" (28.7)

#6-32 - TAP

2.28

(57.9)

1.13" (28.7)

1.25'

(31.8)

HBL1221

1.25" (31.8)

HBL3031


2.33 (59.1


2.33'

3.28" (59.1) (83.2)

3.28" (83.2)

HBL1221L and Key





HBL1222RKL and Key

Dimensions in Inches (mm)