



PROTO®

Item # 1UDY2

Mfr. Model # JTS-0141RR

Set Includes:

Mfg Part #	Description	Qty
J1192-A	WRENCH RAT BOX 3/8 X 7/16 6 P	1
J1193-A	WRENCH RAT BOX 1/2 X 9/16 6 P	1
J1195-A	WRENCH RAT BOX 3/4 X 7/8 12 P	1
J1200FBASD	SET WRENCH COMB 14PC 12PT BLK (set breakdown indented below)	1
J1240BASD	WRENCH COMB 1-1/4 12 PT BLACK	1
J1236BASD	WRENCH COMB 1-1/8 12 PT BLACK	1
J1234BASD	WRENCH COMB 1-1/16 12 PT BLAC	1
J1232BASD	WRENCH COMB 1 12 PT BLACK	1
J1230BASD	WRENCH COMB 15/16 12 PT BLACK	1
J1228BASD	WRENCH COMB 7/8 12 PT BLACK	1
J1226BASD	WRENCH COMB 13/16 12 PT BLACK	1
J1224BASD	WRENCH COMB 3/4 12 PT BLACK	1
J1222BASD	WRENCH COMB 11/16 12 PT BLACK	1
J1220BASD	WRENCH COMB 5/8 12 PT BLACK	1
J1218BASD	WRENCH COMB 9/16 12 PT BLACK	1
J1216BASD	WRENCH COMB 1/2 12 PT BLACK	1
J1214BASD	WRENCH COMB 7/16 12 PT BLACK	1
J1212BASD	WRENCH COMB 3/8 12 PT BLACK	1
J1312AVP	12OZ BALL PEEN HAMMER	1
J209G	PLIER DIAGONAL W/GRIP	1
J2116	BAR PRY ALIGNING 16	1
J226G	PLIER NEEDLE NOSE SIDE CU	1
J4980	SET HEX KEY 13PC	1
J260SGXL	10"GROOVE JOINT	1
J267G	PLIER LINEMANS W/GRIP	1
J291NC	PLIER LOCKING STRAIGHT 7	1
J3200D	SET WRENCH IGNITION 9 PC (set breakdown indented below)	1
J3210	WRENCH ANGLE 13/64 X 15/64 SH	1
J3211	WRENCH ANGLE 15/64 X 13/64 SH	1
J3215	WRENCH ANGLE 7/32 X 1/4 SHORT	1
J3216	WRENCH ANGLE 1/4 X 7/32 SHORT	1
J3220	WRENCH ANGLE 9/32 X 5/16 SHOR	1
J3221	WRENCH ANGLE 5/16 X 9/32 SHOR	1
J3225	WRENCH ANGLE 11/32 X 3/8 SHOR	1
J3226	WRENCH ANGLE 3/8 X 11/32 SHOR	1
J235	PLIER IGNITION W/GRIP	1

Mfg Part #	Description	Qty
JTS-0141RR-1	24 PC SUBSET 1/4DR SOCKETS + ACCY (set breakdown indented below)	1
J4706	SOCKET 1/4 DR 3/16 6 PT	1
J4706L	SOCKET 1/4 DR 3/16 6 PT DEEP	1
J4707	SOCKET 1/4 DR 7/32 6 PT	1
J4707L	SOCKET 1/4 DR 7/32 6 PT DEEP	1
J4708	SOCKET 1/4 DR 1/4 6 PT	1
J4708L	SOCKET 1/4 DR 1/4 6 PT DEEP	1
J4709	SOCKET 1/4 DR 9/32 6 PT	1
J4709L	SOCKET 1/4 DR 9/32 6 PT DEEP	1
J4710	SOCKET 1/4 DR 5/16 6 PT	1
J4710L	SOCKET 1/4 DR 5/16 6 PT DEEP	1
J4711	SOCKET 1/4 DR 11/32 6 PT	1
J4711L	SOCKET 1/4 DR 11/32 6 PT DEEP	1
J4712	SOCKET 1/4 DR 3/8 6 PT	1
J4712L	SOCKET 1/4 DR 3/8 6 PT DEEP	1
J4714	SOCKET 1/4 DR 7/16 6 PT	1
J4714L	SOCKET 1/4 DR 7/16 6 PT DEEP	1
J4716	SOCKET 1/4 DR 1/2 6 PT	1
J4716L	SOCKET 1/4 DR 1/2 6 PT DEEP	1
J4718	SOCKET 1/4 DR 9/16 6 PT	1
J4718L	SOCKET 1/4 DR 9/16 6 PT DEEP	1
J4759	EXTENSION 1/4 DR 2	1
J4761	EXTENSION 1/4 DR 6	1
J4769	DRIVER SOCKET 1/4 DR	1
J4770A	1/4 Dr. Universal Joint	1
JTS-0141RR-2	40PC SUBSET 3/8-1/2DR SOCKETS + A (set breakdown indented below)	1
J5012B	SOCKET 3/8 DR 3/8 12 PT DEEP	1
J5014B	SOCKET 3/8 DR 7/16 12 PT DEE	1
J5016B	SOCKET 3/8 DR 1/2 12 PT DEEP	1
J5018B	SOCKET 3/8 DR 9/16 12 PT DEE	1
J5020B	SOCKET 3/8 DR 5/8 12 PT DEEP	1
J5022B	SOCKET 3/8 DR 11/16 12 PT DE	1
J5024B	SOCKET 3/8 DR 3/4 12 PT DEEP	1
J5212B	SOCKET 3/8 DR 3/8 12 PT BLAC	1

Mfg Part #	Description	Qty
J5214B	SOCKET 3/8 DR 7/16 12 PT BLA	1
J5216B	SOCKET 3/8 DR 1/2 12 PT BLAC	1
J5218B	SOCKET 3/8 DR 9/16 12 PT BLA	1
J5220B	SOCKET 3/8 DR 5/8 12 PT BLAC	1
J5222B	SOCKET 3/8 DR 11/16 12 PT BL	1
J5224B	SOCKET 3/8 DR 3/4 12 PT BLAC	1
J5249BL	RATCHET 3/8 DR BLACK	1
J5260-06B	EXTENSION 3/8 DR 6 BLACK	1
J5260B	EXTENSION 3/8 DR 3 BLACK	1
J5273A	3/8 Dr. 12 Point, 3/8	1
J5274A	3/8 DR 12 Point 7/16	1
J5275A	3/8 Dr. 12 Point, 1/2	1
J5276A	3/8 Dr. 12 Point, 9/16	1
J5414B	SOCKET 1/2 DR 7/16 12 PT BLA	1
J5416B	SOCKET 1/2 DR 1/2 12 PT BLAC	1
J5418B	SOCKET 1/2 DR 9/16 12 PT BLA	1
J5420B	SOCKET 1/2 DR 5/8 12 PT BLAC	1
J5422B	SOCKET 1/2 DR 11/16 12 PT BL	1
J5424B	SOCKET 1/2 DR 3/4 12 PT BLAC	1
J5426B	SOCKET 1/2 DR 13/16 12 PT BL	1
J5428B	SOCKET 1/2 DR 7/8 12 PT BLAC	1
J5430B	SOCKET 1/2 DR 15/16 12 PT BL	1
J5432B	SOCKET 1/2 DR 1 12 PT BLACK	1
J5434B	SOCKET 1/2 DR 1-1/16 12 PT B	1
J5436B	SOCKET 1/2 DR 1-1/8 12 PT BL	1
J5440B	SOCKET 1/2 DR 1-1/4 12 PT BL	1
J5449BL	RATCHET 1/2 DR BLACK	1
J5461B	EXTENSION 1/2 DR 5 BLACK	1
J5463B	EXTENSION 1/2 DR 10 BLACK	1
J5468BL	HANDLE HINGE 1/2 DR 18-5/	1
J77270P	3/8DR IMP UNV JOINT 3/8 X 3/8	1
J74470P	1/2DR IMP UNV JOINT	1
J4749BL	RATCHET 1/4 DR BLACK	1
J708B	WRENCH ADJUSTABLE 8	1
J706B	WRENCH ADJUSTABLE 6	1
10-099	ST KNF RETRACT CARDED	1
J299	PLIER WIRE STRIPPERS	1
33-725	FM TAPE CD 25' 1/4"	1
J9866	SCREW STARTER DBL END	1
J2108	HOLDER PUNCH + CHISEL	1
J48116	PUNCH PIN 1/16 SUPER DUTY	1
J48038	PUNCH PIN 3/8 SUPER DUTY	1
J48532	PUNCH PIN 5/32 SUPER DUTY	1
J5265BL	HANDLE HINGE 3/8 DR 7-7/8	1
J5028B	SOCKET 3/8 DR 7/8 12 PT DEEP	1

Mfg Part #	Description	Qty
J5210B	SOCKET 3/8 DR 5/16 12 PT BLA	1
J5412B	SOCKET 1/2 DR 3/8 12 PT BLAC	1
J1207SNDS	7PC SAE HOLLOW NUT DRIVER (set breakdown indented below)	1
JN113204RS	11/32IN X 4IN SAE NUTDRIVER	1
JN1204RS	1/2IN X 4IN SAE NUTDRIVER	1
JN1404RS	1/4IN X 4IN SAE NUTDRIVER	1
JN31604RS	3/16IN X 4IN SAE NUTDRIVE	1
JN3804RS	3/8IN X 4IN SAE NUTDRIVER	1
JN51604RS	5/16IN X 4IN SAE NUTDRIVE	1
JN71604RS	7/16IN X 4IN SAE NUTDRIVE	1
JKB1404RPF	1/4X4IN BOLSTER KEYSTN RD HP BR	1
JKB31604RPF	SCREWDRIVER SLOTTED KEYSTONE RD 3/16X4	1
JKB51606RPF	5/16X6IN BOLSTER KEYSTONE ROUND BAR	1
JKB3808RPF	3/8X8IN BOLSTER KEYSTONE ROUND BAR	1
JK3810RF	3/8X10IN KEYSTONE ROUND BAR	1
JP0103RF	NO1 X 3IN PHILLIPS ROUND BAR	1
JP0204RF	NO 2 X 4IN PHILLIPS ROUND BAR	1