



PROTO®

Item # 1UDY3

Mfr. Model # JTS-0172RR

Set Includes:

Mfg Part #	Description	Qty
J000AA	SET FEELER GAUGE 25 BLADE	1
J1195-A	WRENCH RAT BOX 3/4 X 7/8 12 P	1
J1208EFS	1/4 WRENCH COMB SHORT 6PT	1
J1209EFS	9/32 WRENCH COMB SHORT 6PT	1
J1210EFS	5/16 WRENCH COMB SHORT 6PT	1
J1200FBASD	SET WRENCH COMB 14PC 12PT BLK (set breakdown indented below)	1
J1240BASD	WRENCH COMB 1-1/4 12 PT BLACKw	1
J1236BASD	WRENCH COMB 1-1/8 12 PT BLACK	1
J1234BASD	WRENCH COMB 1-1/16 12 PT BLAC	1
J1232BASD	WRENCH COMB 1 12 PT BLACK	1
J1230BASD	WRENCH COMB 15/16 12 PT BLACK	1
J1228BASD	WRENCH COMB 7/8 12 PT BLACK	1
J1226BASD	WRENCH COMB 13/16 12 PT BLACK	1
J1224BASD	WRENCH COMB 3/4 12 PT BLACK	1
J1222BASD	WRENCH COMB 11/16 12 PT BLACK	1
J1220BASD	WRENCH COMB 5/8 12 PT BLACK	1
J1218BASD	WRENCH COMB 9/16 12 PT BLACK	1
J1216BASD	WRENCH COMB 1/2 12 PT BLACK	1
J1214BASD	WRENCH COMB 7/16 12 PT BLACK	1
J1212BASD	WRENCH COMB 3/8 12 PT BLACK	1
J1244B	WRENCH COMB 1-3/8 12 PT BLACK	1
J1246B	WRENCH COMB 1-7/16 12 PT BLAC	1
J1248B	WRENCH COMB 1-1/2 12 PT BLACK	1
J1316AVP	16OZ BALL PEEN HAMMER	1
J1730	WRENCH OBSTRUCTION 9/16 X 5/8	1
J1731	WRENCH OBSTRUCTION 5/8 X 3/4	1
J209G	PLIER DIAGONAL W/GRIP	1
J2108	HOLDER PUNCH + CHISEL	1
J2116	BAR PRY ALIGNING 16	1
J2126	BAR 12IN LONG 1/2IN TIP	1
J226G	PLIER NEEDLE NOSE SIDE CU	1
J2345	RETRIEVER + HOLDER FLEX	1
J2375	RETRIEVER MAG 16-3/4 TELE	1
J260SGXL	10" GROOVE JOINT	1
J265SGXL	16" GROOVE JOINT	1
J278GXL	8" PLIER SLIP-JOINT W/GRIP(NATURAL FINISH	1
J291NC	PLIER LOCKING STRAIGHT 7	1
J292XL	PLIERS LOCKING CURVED 10	1

Mfg Part #	Description	Qty
J298	PLIER WIRE STRIPPERS	1
J380	SET PLIER RETAINING RING	1
J3800A	SET WRENCH FLARE NUT RATCHET (set breakdown indented below)	1
J3824	WRENCH FLARE NUT RATCH 3/4 12	1
J3822	WRENCH FLARE NUT RATCH 11/16	1
J3820	WRENCH FLARE NUT RATCH 5/8 12	1
J3818	WRENCH FLARE NUT RATCH 9/16 1	1
J3816	WRENCH FLARE NUT RATCH 1/2 12	1
J3814	WRENCH FLARE NUT RATCH 7/16 1	1
J3812	WRENCH FLARE NUT RATCH 3/8 12	1
J415/16S2	PUNCH CENTER 5/16	1
J4980	SET HEX KEY 13PC	1
J52110H	3/8 & 1/2 DR 10PC SAE HEX (set break-down indented below)	1
J49901/4	SOCKET HEX BIT 3/8 DR 1/4	1
J49901/8	SOCKET HEX BIT 3/8 DR 1/8	1
J49903/16	SOCKET HEX BIT 3/8 DR 3/16	1
J49903/8	SOCKET HEX BIT 3/8 DR 3/8	1
J49905/16	SOCKET HEX BIT 3/8 DR 5/16	1
J49905/32	SOCKET HEX BIT 3/8 DR 5/32	1
J49907/32	SOCKET HEX BIT 3/8 DR 7/32	1
J54411/2	SOCKET HEX BIT 1/2 DR 1/2	1
J54415/8	SOCKET HEX BIT 1/2 DR 5/8	1
J54419/16	SOCKET HEX BIT 1/2 DR 9/16	1
JTS-0172RR-1	25PC SUBSET 3/8DR SOCKETS + ACCYS (set breakdown indented below)	1
J5014B	SOCKET 3/8 DR 7/16 12 PT DEE	1
J5016B	SOCKET 3/8 DR 1/2 12 PT DEEP	1
J5018B	SOCKET 3/8 DR 9/16 12 PT DEE	1
J5020B	SOCKET 3/8 DR 5/8 12 PT DEEP	1
J5022B	SOCKET 3/8 DR 11/16 12 PT DE	1
J5024B	SOCKET 3/8 DR 3/4 12 PT DEEP	1
J5210B	SOCKET 3/8 DR 5/16 12 PT BLA	1
J5212B	SOCKET 3/8 DR 3/8 12 PT BLAC	1
J5214B	SOCKET 3/8 DR 7/16 12 PT BLA	1

Mfg Part #	Description	Qty
J5216B	SOCKET 3/8 DR 1/2 12 PT BLAC	1
J5218B	SOCKET 3/8 DR 9/16 12 PT BLA	1
J5220B	SOCKET 3/8 DR 5/8 12 PT BLAC	1
J5222B	SOCKET 3/8 DR 11/16 12 PT BL	1
J5224B	SOCKET 3/8 DR 3/4 12 PT BLAC	1
J5246	SOCKET BIT 3/8 DR SLOTTED	1
J5249BL	RATCHET 3/8 DR BLACK	1
J5259B	EXTENSION 3/8 DR 1-3/4 BL	1
J5260-06B	EXTENSION 3/8 DR 6 BLACK	1
J5260B	EXTENSION 3/8 DR 3 BLACK	1
J5261B	EXTENSION 3/8 DR 8 BLACK	1
J5270A	3/8 Dr. Universal Joint	1
J5273A	3/8 Dr. 12 Point, 3/8	1
J5274A	3/8 DR 12 Point 7/16	1
J5275A	3/8 Dr. 12 Point, 1/2	1
J5276A	3/8 Dr. 12 Point, 9/16	1
JTS-0172RR-2	33PC SUBSET 1/2DR SOCKET + ACCYS (set breakdown indented below)	1
J5416B	SOCKET 1/2 DR 1/2 12 PT BLAC	1
J5418B	SOCKET 1/2 DR 9/16 12 PT BLA	1
J5420B	SOCKET 1/2 DR 5/8 12 PT BLAC	1
J5422B	SOCKET 1/2 DR 11/16 12 PT BL	1
J5424B	SOCKET 1/2 DR 3/4 12 PT BLAC	1
J5426B	SOCKET 1/2 DR 13/16 12 PT BL	1
J5428B	SOCKET 1/2 DR 7/8 12 PT BLAC	1
J5430B	SOCKET 1/2 DR 15/16 12 PT BL	1
J5432B	SOCKET 1/2 DR 1 12 PT BLACK	1
J5434B	SOCKET 1/2 DR 1-1/16 12 PT B	1
J5436B	SOCKET 1/2 DR 1-1/8 12 PT BL	1
J5440B	SOCKET 1/2 DR 1-1/4 12 PT BL	1
J5442B	SOCKET 1/2 DR 1-5/16 12 PT B	1
J5444B	SOCKET 1/2 DR 1-3/8 12 PT BL	1
J5446B	SOCKET 1/2 DR 1-7/16 12 PT B	1
J5448B	SOCKET 1/2 DR 1-1/2 12 PT BL	1
J5449BL	RATCHET 1/2 DR BLACK	1
J5460B	EXTENSION 1/2 DR 2-1/2 BL	1
J5461B	EXTENSION 1/2 DR 5 BLACK	1
J5463B	EXTENSION 1/2 DR 10 BLACK	1
J5470A	UNIVERSAL JOINT 1/2 DR	1
J5322B	SOCKET 1/2 DR 11/16 12 PT DE	1
J5324B	SOCKET 1/2 DR 3/4 12 PT DEEP	1
J5326B	SOCKET 1/2 DR 13/16 12 PT DE	1
J5328B	SOCKET 1/2 DR 7/8 12 PT DEEP	1
J5330B	SOCKET 1/2 DR 15/16 12 PT DE	1
J5332B	SOCKET 1/2 DR 1 12 PT DEEP B	1
J5334B	SOCKET 1/2 DR 1-1/16 12 PT D	1

Mfg Part #	Description	Qty
J5336B	SOCKET 1/2 DR 1-1/8 12 PT DE	1
J5414B	SOCKET 1/2 DR 7/16 12 PT BLA	1
J5316B	SOCKET 1/2 DR 1/2 12 PT DEEP	1
J5318B	SOCKET 1/2 DR 9/16 12 PT DEE	1
J5320B	SOCKET 1/2 DR 5/8 12 PT DEEP	1
J725/16S2	CHISEL CAPE 13/64	1
J810HD	WRENCH PIPE 10	1
J818HD	WRENCH PIPE 18	1
J961/2S2	PUNCH DRIFT 1/4	1
J965/16S2	PUNCH DRIFT 1/8	1
J9853	SCREW STARTER STD TIP 5-5	1
JSF200	HAMMER SOFT FACE W/O TIPS	1
JSF20T	HAMMER TIP 2 TOUGH	1
20-531	FM 12IN HACKSAW	1
JKB1404RPF	1/4X4IN BOLSTER KEYSTN RD HP BR	1
JKB51606RPF	5/16X6IN BOLSTER KEYSTONE ROUND BAR	1
JKB3808RPF	3/8X8IN BOLSTER KEYSTONE ROUND BAR	1
JK3810RF	3/8X10IN KEYSTONE ROUND BAR	1
JP02112RF	NO2X1.5IN PHILLPS ROUND BAR	1
JP0204RF	NO 2 X 4IN PHILLIPS ROUND BAR	1
J708B	WRENCH ADJUSTABLE 8	1
J712SB	WRENCH ADJUSTABLE 12 BLACK	1
J715SB	WRENCH ADJUSTABLE 15 BLACK	1
J48116	PUNCH PIN 1/16 SUPER DUTY	1
J48018	PUNCH PIN 1/8 SUPER DUTY	1
J48532	PUNCH PIN 5/32 SUPER DUTY	1
J48038	PUNCH PIN 3/8 SUPER DUTY	1
J48316	PUNCH PIN 3/16 SUPER DUTY	1
J86038	CHISEL COLD 3/8 SUPER DUT	1
J86012	CHISEL COLD 1/2 SUPER DUT	1
J86001	CHISEL COLD 1 SUPER DUTY	1