



BALLAST IGNITOR



Model no.	Lamp Type	No. of Lamps	Case Temperature rating	Lamp Watts	Dimensions		Max. Distance to Lamp (ft.)
					Length (In.)	Width (In.)	
1XUG2	Metal Halide	1	105C	35-150, 175-450 Pulse Start	2-1/2	1-3/4	2-25
1XUG3	High Pressure Sodium	1	105C	35-150	2-1/2	1-3/4	2
1XUG4	High Pressure Sodium	1	105C	150-400	2-1/2	1-3/4	2
1XUG5	High Pressure Sodium	1	105C	1000	4 -3/4	2 -5/32	15



1XUG4
HPSR24



E241536

USE WITH 200-400W HPS
BALLAST MOUNTED IN FIXTURE
10FT. MAX LAMP TO BALLAST
105C MAX. CASE TEMP.

RED -- X1 (To Lamp on BALLAST Side)
WHITE -- X2 (To COM on BALLAST Side)
BLUE -- X3 (To X3 on BALLAST Side)

Mfg. for Grainger International Inc.
Lake Forest, IL 60045
Made in China

CONTAINS BLEEDER RESISTOR FOR DISCHARGING CAPACITORS CONNECTED EXTERNALLY.