

# SPLASH MOUNT PRE-RINSE UNITS

## KN53-1000 • KL53-1000 SERIES

1	KL53-Y001	FAUCET BODY ASSEMBLY
2	KL50-Y007	HOT VALVE ASSEMBLY – ¼ TURN – COMPRESSION
	KL50-Y007-CCV	HOT VALVE ASSEMBLY – ¼ TURN – CERAMIC
	KL50-Y007-KT	HOT VALVE ASSEMBLY – ¼ TURN – COMPRESSION – WITH HANDLE
	KL50-Y007CVKT	HOT VALVE ASSEMBLY – ¼ TURN – CERAMIC – WITH HANDLE
3	KL50-Y006	COLD VALVE ASSEMBLY – ¼ TURN – COMPRESSION
	KL50-Y006-CCV	COLD VALVE ASSEMBLY – ¼ TURN – CERAMIC
	KL50-Y006-KT	COLD VALVE ASSEMBLY – ¼ TURN – COMPRESSION – WITH HANDLE
	KL50-Y006CVKT	COLD VALVE ASSEMBLY – ¼ TURN – CERAMIC – WITH HANDLE
4	K50-0110	LEVER HANDLE REPLACEMENT KIT W/SCREW
	K50-0001	WRIST BLADE HANDLES, PAIR, 4"
	K50-0001-6	WRIST BLADE HANDLES, PAIR, 6"
5	KL40-1000	MOUNTING KIT
	KL40-2020	MOUNTING KIT, CLOSE ELBOWS
6	K50-Y011	HOOK/SCREW ASSEMBLY
7	K50-Y020	WALL BRACKET ASSEMBLY
	K50-Y020-6	WALL BRACKET ASSEMBLY, 6"
8	KL50-X077	RISER, 18"
	KL50-X029	RISER, 24"
9	KL50-X032	SPRING RETAINER
10	K50-X033	SPRING
	K50-X178	SPRING, STAINLESS STEEL
11	KL50-Y004-20	HOSE ASSEMBLY WITH GRIP – 20"
	KL50-Y004-26	HOSE ASSEMBLY WITH GRIP – 26"
	KL50-Y004-36	HOSE ASSEMBLY WITH GRIP – 36"
	KL50-Y004-44	HOSE ASSEMBLY WITH GRIP – 44"
	KL50-Y004-60	HOSE ASSEMBLY WITH GRIP – 60"
	KL50-Y004-72	HOSE ASSEMBLY WITH GRIP – 72"
	KL50-Y004-96	HOSE ASSEMBLY WITH GRIP – 96"
12	KL50-Y010-20	HOSE ASSEMBLY ONLY – 20"
	KL50-Y010-26	HOSE ASSEMBLY ONLY – 26"
	KL50-Y010-36	HOSE ASSEMBLY ONLY – 36"
	KL50-Y010-44	HOSE ASSEMBLY ONLY – 44"
	KL50-Y010-60	HOSE ASSEMBLY ONLY – 60"
	KL50-Y010-72	HOSE ASSEMBLY ONLY – 72"
	KL50-Y010-96	HOSE ASSEMBLY ONLY – 96"
13	KN50-X025	GRIP
14	KL50-Y002-065	PRE-RINSE SPRAY ASSEMBLY – .65 GPM
	KL50-Y002-12	PRE-RINSE SPRAY ASSEMBLY – 1.2 GPM
	KL50-Y002-16	PRE-RINSE SPRAY ASSEMBLY – 1.6 GPM
15	KL50-Y027	BUTTON VALVE ASSEMBLY
16	KL50-0200-16	SPRAY HEAD REPAIR KIT 1.6 GPM
17	KN50-X135	WATER SAVER FACE PLATE – 1.6 GPM
	KN50-X135-12	WATER SAVER FACE PLATE – 1.2 GPM
	KN50-X135-065	WATER SAVER FACE PLATE – .65 GPM

