

Technical data

Voltage	U	240	V
Phase		1	~
Frequency		60	Hz
Speed		1580	RPM
Power consumption	P _e	430	W
Nominal current	I	1.8	A
Maximum current	I	2.2	A
Capacitor		20/250	µF
Ambient temperature	T _{amb min/max}	-13...104	°F
Insulation Class		CL.F	
IP Class Fan		IP55	
Sound pressure level	L _p	66	db(A)
Sound pressure level distance		6.6	ft
Weight		31.2	Lbs.
Packing dimensions		26.4x26.4x12.4	inch

Fan details


Impeller blades	6
Impeller type	3
Impeller system	C
Impeller material	PP

Control options

Triac controller	Yes
Transformer	Yes
Frequency drive	No
Intelligent Fan Drive	No

Characteristics

0.00 in. wg	4914 CFM
0.20 in. wg	4237 CFM




Please note: Picture may deviate from original product

Approval(s)




Wiring diagram - Fan

AA07 - 1 Phase - Dual-voltage - High Voltage - CCW



Dimensions



A01	20.2 inch
A02	25.5 inch
A03	25.5 inch
A04	23.6 inch
A05	23.6 inch
A06	7.6 inch
A07	21.3 inch
A08	3.3 inch
A09	1.4 inch
A10	0.3 inch