

**AMERIC CONFINED SPACE VENTILATOR**  
**VAF3000B**

**Product Description**

Industrial VAF3000A/B – On-demand performance. Ideal for use in confined spaces that require a powerhouse air ventilator, the VAF3000A/B can handle your most demanding industrial needs. With a forceful 1 hp motor, the VAF3000 can deliver both positive and negative airflow at an incredible maximum capacity of 2,796 CFM in the most difficult work environments!

**Features**

- Industry leading airflow in all sizes, rated from 750-10,000 cfm
- Dual wall polyethylene housing designed to withstand the harshest of conditions, providing years of durability and dependability
- Premium quality motors rated for over 100,000 hours of heavy duty, continuous use for unmatched return on investment
- Safety tested to UL, CSA and CE certifications, exceeding industry standards
- Provides positive and negative airflow (blows and extracts)
- Lightweight for easy portability
- Stackable to save storage space
- Three year warranty
- Made in the USA



**Specifications**

Blade Color	Black
Brand	Schaefer
Cfm (free Air)	2492
Cfm (with 25' Of Duct)	1830
Drive	Direct
Housing Material	Polyethylene
Maximum Duct Length (feet)	125
Phase	1
Speeds	1
Cfm/watt (free Air)	4.1
Cord	Included - Wired
Diameter (inches)	12
Frequency (hz)	50

Guard Color	Black
Nameplate Amps	4.2
Number Of Wings	7
Power (hp)	1
Product Dimensions (L X W X H Inches)	21" x 17" x 14"
Product Net Weight (lbs)	32.5
Performance Test #	497
Switch	On product
Voltage	220
Blade Material	Polypropylene
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	Blue
Product Shipping Dimensions (in)	18 x 16 x 24

Able To Ship Small Parcel	Yes
Cfm Range (free Air)	1001 - 2500
Cord Length (feet)	20
Distinguishing Feature	Suitable with Ducting
Fixed Or Portable	Portable
Guard Material	Powder Coated Steel
Oscillating	No
Product Certifications	cULus/CE
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA
Housing Color	Blue
Maximum Static Pressure (in. H2o)	2.5