


# Cush-A-Clamp®



Gold Electro-Galvanized Steel



Stainless Steel



Steel Part No.	Stainless Steel Part No.	Dimension "A"			Dimensions (inches)			
		*Copper and Steel Tubing	Copper Water Pipe (Nom.)	Nom. Pipe Size	A	B	C	D
004T008	004NS008	1/4"	-	-	0.25" (6mm)	0.62" (16mm)	0.27" (7mm)	0.98" (25mm)
006T010	006NS010	3/8"	1/4"	-	0.37" (9mm)	0.82" (21mm)	0.33" (8mm)	1.13" (29mm)
008T012	008NS012	1/2"	3/8"	-	0.50" (13mm)	0.94" (24mm)	0.40" (10mm)	1.34" (34mm)
009N012	009NS012	-	-	1/4"	0.54" (14mm)	0.98" (25mm)	0.43" (11mm)	1.34" (34mm)
010T014	010NS014	5/8"	1/2"	-	0.62" (16mm)	1.06" (27mm)	0.46" (12mm)	1.54" (39mm)
011N014	011NS014	-	-	3/8"	0.67" (17mm)	1.13" (29mm)	0.49" (12mm)	1.54" (39mm)
012T016	012NS016	3/4"	5/8"	-	0.75" (19mm)	1.20" (30mm)	0.52" (13mm)	1.68" (43mm)
014N018	014NS018	-	-	1/2"	0.84" (21mm)	1.29" (33mm)	0.58" (15mm)	1.82" (46mm)
014T018	014NS018	7/8"	3/4"	-	0.87" (22mm)	1.31" (33mm)	0.58" (15mm)	1.82" (46mm)
016T020	016NS020	1"	-	-	1.00" (25mm)	1.44" (37mm)	0.65" (17mm)	1.95" (50mm)
017N022	017NS022	-	-	3/4"	1.05" (27mm)	1.57" (40mm)	0.70" (18mm)	2.08" (53mm)
018T022	018NS022	1-1/8"	1"	-	1.12" (28mm)	1.57" (40mm)	0.70" (18mm)	2.08" (53mm)
020T024	020NS024	1-1/4"	-	-	1.25" (32mm)	1.70" (43mm)	0.77" (20mm)	2.21" (56mm)
021N026	021NS026	-	-	1"	1.31" (33mm)	1.76" (45mm)	0.81" (21mm)	2.34" (59mm)
022T026	022NS026	1-3/8"	1-1/4"	-	1.37" (35mm)	1.82" (46mm)	0.83" (21mm)	2.34" (59mm)
024N028	024NS028	1-1/2"	-	-	1.50" (38mm)	1.95" (50mm)	0.90" (23mm)	2.47" (63mm)
026N030	026NS030	1-5/8"	1-1/2"	-	1.62" (41mm)	2.07" (53mm)	0.96" (24mm)	2.60" (66mm)
027N032	027NS032	-	-	1-1/4"	1.66" (42mm)	2.17" (55mm)	0.99" (25mm)	2.73" (69mm)
028N032	028NS032	1-3/4"	-	-	1.75" (44mm)	2.2" (56mm)	1.02" (26mm)	2.73" (69mm)
030N034	030NS034	1-7/8"	-	1-1/2"	1.90" (48mm)	2.32" (59mm)	1.09" (28mm)	2.86" (73mm)
032N036	032NS036	2"	-	-	2.00" (51mm)	2.45" (62mm)	1.15" (29mm)	3.04" (77mm)
034N040	034NS040	2-1/8"	2"	-	2.12" (54mm)	2.57" (65mm)	1.27" (32mm)	3.23" (82mm)
038N042	038NS042	2-1/4"	-	-	2.37" (60mm)	2.82" (72mm)	1.41" (36mm)	3.67" (93mm)
038N044	038NS044	2-3/8"	-	2"	2.37" (60mm)	2.82" (72mm)	1.41" (36mm)	3.67" (93mm)
040N046	040NS046	2-1/2"	-	-	2.50" (64mm)	2.94" (75mm)	1.46" (37mm)	3.79" (96mm)
042N048	042NS048	2-5/8"	2-1/2"	-	2.62" (67mm)	3.07" (78mm)	1.53" (39mm)	3.92" (100mm)
046N052	046NS052	2-7/8"	-	2-1/2"	2.87" (73mm)	3.32" (84mm)	1.66" (42mm)	4.17" (106mm)
050N054	050NS054	3"	-	-	3.00" (76mm)	3.57" (91mm)	1.78" (45mm)	4.42" (112mm)
050N056	050NS056	3-1/8"	3"	-	3.12" (79mm)	3.57" (91mm)	1.78" (45mm)	4.42" (112mm)
053N060	053NS060	3-5/16"	-	-	3.31" (84mm)	3.96" (101mm)	1.90" (48mm)	4.75" (121mm)
056N062	056NS062	3-1/2"	-	3"	3.50" (89mm)	3.95" (100mm)	1.97" (50mm)	4.79" (122mm)
058N064	058NS064	3-5/8"	3-1/2"	-	3.62" (92mm)	4.20" (107mm)	2.03" (52mm)	5.11" (130mm)
064N072	064NS072	4"	-	3-1/2"	4.00" (102mm)	4.45" (113mm)	2.28" (58mm)	5.11" (130mm)
066N074	066NS074	4-1/8"	4"	-	4.12" (105mm)	4.57" (116mm)	2.34" (59mm)	5.54" (141mm)
069N076	069NS076	4-5/16"	-	-	4.34" (110mm)	4.96" (126mm)	2.40" (61mm)	5.84" (148mm)
072N080	072NS080	4-1/2"	-	4"	4.50" (114mm)	4.95" (126mm)	2.53" (64mm)	5.92" (150mm)
082N090	082NS090	5-1/8"	5"	-	5.12" (130mm)	5.57" (141mm)	2.84" (72mm)	6.54" (166mm)
089N096	089NS096	-	-	5"	5.56" (141mm)	6.01" (153mm)	3.06" (78mm)	6.92" (176mm)
096N106	096NS106	6"	-	-	6.00" (152mm)	6.57" (167mm)	3.34" (85mm)	7.54" (192mm)
098N106	098NS106	6-1/8"	6"	-	6.12" (155mm)	6.57" (167mm)	3.34" (85mm)	7.54" (192mm)
106N114	106NS114	-	-	6"	6.62" (168mm)	7.07" (180mm)	3.59" (91mm)	8.23" (209mm)

\*Tube O.D. is Cushion I.D. ; Design load deflection data available on request.



**WARNING:** These products can expose you to chemicals including lead, which is known to the State of California to cause cancer, and which is known to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).