

# NSYTRAC22

Lineryg terminal blocks, end cover, for NSYTRV22, NSYTRV42 and NSYTRV terminal blocks, 2.2 mm wide, grey



## Main

Range	Lineryg
Product name	Lineryg TR
Product or Component Type	Cover plate
Device short name	TRA
Accessory / separate part category	Insulation accessory
Product compatibility	TRV screw terminal - passthrough terminal block TRV screw terminal - protective earth terminal block TRV screw terminal - blade disconnect terminal block
Thickness	0.09 in (2.2 mm)

## Complementary

Cable cross section	0.01 In <sup>2</sup> (6 mm <sup>2</sup> ) 0.00 In <sup>2</sup> (2.5 mm <sup>2</sup> ) 0.01 In <sup>2</sup> (4 mm <sup>2</sup> ) 0.02 in <sup>2</sup> (10 mm <sup>2</sup> )
Number of connections	2
Number of measurement input	2 1
Quantity per Set	Set of 50
Net Weight	0.08 oz (2.4 g)
Color	Gray

## Ordering and shipping details

Category	21715 - IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
Discount Schedule	CP5
GTIN	3606480533549
Nbr. of units in pkg.	1
Package weight(Lbs)	0.09 oz (2.56 g)
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.16 in (0.4 cm)
Package 1 width	1.81 in (4.6 cm)
Package 1 Length	1.54 in (3.9 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	50
Package 2 Weight	4.48 oz (127 g)
Package 2 Height	1.18 in (3 cm)
Package 2 width	5.12 in (13 cm)
Package 2 Length	6.69 in (17 cm)
Unit Type of Package 3	S04
Number of Units in Package 3	3600

Package 3 Weight	21.94 lb(US) (9.95 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product

### Contractual warranty

Warranty	18 months
----------	-----------