







Our first hand-held, lithium battery-powered **programmable** flashlight that provides **600 lumens** of light with **253 meters** of beam distance.

FL1 STANDARD	HIGH	LOW
	600 LUMENS	33 LUMENS
	1h 15min	18h
	253m	57m
	16,000cd	800cd

Strobe runs 2.5 hours

TEN-TAP™ Programming: Choice of three operating modes: 1.) high/strobe/low (factory default); 2.) high only, 3.) low/high
Optimized electronics provide regulated intensity
Removable pocket clip
IPX7; waterproof to 1 meter for 30 minutes, 1 meter impact resistance tested
Barrel diameter: 1.0" (2.54 cm); Length: 5.40 in. (13.72 cm) 5.6 oz (158 grams) with batteries
Limited lifetime warranty
#88040 - ProTac HL with lithium batteries and nylon holster

