



Z843M1

Sink Faucet

TAG _____

Architectural/Engineering Specification:

Polished chrome-plated cast brass 8" [203mm] sink faucet with quarter turn ceramic disc cartridges, 3/8" [10mm] short swivel inlets providing adjustable centers from 7-1/4" [184mm] to 8-3/4" [222mm], integral service stops and a 6" [152mm] centerline cast brass spout with chemical resistant atmospheric vacuum breaker, 3/4" hose threaded outlet, pail hook and adjustable wall brace. Unit is furnished with 2-1/2" [64mm] vandal-resistant color-coded brass lever handles. Vacuum breaker is certified to the uniform plumbing code®, ASSE 1001- 2002 and CSA b64-01. (note: atmospheric vacuum breaker not intended for continuous pressure applications.)

Product Features:

- 8" Vacuum Breaker Spout with 3/4" Threaded Outlet, Brace and Pail Hook
- 2-1/2" Vandal Resistant Color Coded Lever Handles
- Ceramic Disc Cartridge
- Chrome-plated Cast Brass Body

Compliance and Certification:

- ADA Compliant
- ASSE 1001- 2002
- CSA b64-01



Suffix Options:

- CS Check Stop
- FC 2.0 GPM [7.6 L] Laminar Flow Control in Base of Spout
- FC _____ Plain End Spout with Flow Control (Specify GPM Flow: 0.5, 1.0, 1.5)
- LSI 2-1/2" [64mm] Long Swivel Inlets with Integral Stops
- RC Rough Chrome Plated
- WHK Wall Hook
- 5H 5' [152cm] Vinyl Hose
- 6P Master Carton (Qty. 6)
- Other

Architectural/Engineering Approval

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.





Z843M1

Sink Faucet

TAG _____

Rough-in dimensions/Overview dimensions

