

PC 600 SILVER

Shurtape®
TRUE TO YOUR WORK™

ALL-PURPOSE GRADE, CO-EXTRUDED CLOTH DUCT TAPE

TYPICAL APPLICATIONS

- For general purpose use in industrial, carpet, plumbing, HVAC, sealing, waterproofing, patching, remediation and restoration applications

PRODUCT FEATURES

- Conformable
- Will not twist or curl during application
- Hand-tearable
- High tack
- Made using Polybonded CO-EX Technology®

CONSTRUCTION

Overall Grade/Function: All-purpose

Backing: Polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	22 lbs/in width	38.5 N/10 mm
Adhesion to Stainless Steel	50 oz/in width	5.47 N/10 mm
Thickness	9 mils	0.23 mm
Elongation	16%	16%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

