

Deadbolt - 185 Series



360° turn of the key or thumbturn retracts the bolt. The bolt provides maximum security on single leaf aluminum stile doors and will retrofit to existing locks previously installed. Accepts standard $1\frac{5}{32}$ " (29.4 mm) diameter mortise cylinder or thumbturn with AR cam. Available with straight bolt (185) and hook bolt (HB185).

Features:

- Plating on steel case resist corrosion
- Hardened steel pin installed inside bolt core to prevent sawing.
- Quality assured: Cycle tested to exceed ANSI Grade 1 standards
- Locksets include two faceplates of the most popular finishes. One set covers 90 percent of door finishes

Grainger Item Numbers:

| | |
|-------------------------------------|--|
| 25AK33 (185-F-3NH-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS Deadbolt Set includes two flat faceplates, 628 and 313 finishes |
| 25AK35 (185-F-4NH-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS Deadbolt Set includes two flat faceplates, 628 and 313 finishes |
| 25AK34 (HB185-F-3NH-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS Hookbolt Set includes two flat face plates, 628 and 313 finishes |
| 25AK36 (HB185-F-4NH-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS Hookbolt Set includes two flat faceplates, 628 and 313 finishes |

Deadlatch- 451 Series



Offers flexibility of traffic control for buildings that require free entrance during specific times and exit only at other times. A reverse turn of the key, while the bolt is retracted, retains the bolt for two-way traffic. Accepts standard $1\frac{5}{32}$ " (29.4 mm) diameter mortise cylinder or thumbturn with AR cam. Interchangeable with 185 series deadbolts or other locks previously installed.

Features:

- Plating on steel case resist corrosion
- Supplied pre-handed, but field reversible for versatility
- Quality assured: Cycle tested to exceed ANSI Grade 1 standards
- Locksets include two faceplates of the most popular finishes. One set covers 90 percent of door finishes.

Grainger Item Numbers:

| | |
|---------------------------------------|---|
| 25AK37 (451-F-3LH-201-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS, Left Handed Deadlatch set that includes a 4502-01 short lip standard strike, a 628 and 313 flat faceplate |
| 25AK38 (451-F-3RH-201-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS, Right Handed Deadlatch set that includes a 4502-01 short lip standard strike, a 628 and 313 flat faceplate |
| 25AK39 (451-F-3LH-101-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS, Left Handed Deadlatch set that includes a 4501-01 long lip standard strike, a 628 and 313 flat faceplate |
| 25AK40 (451-F-3RH-101-628/313) | 1 $\frac{1}{8}$ " (28.58 mm) BS, Right Handed Deadlatch set that includes a 4501-01 long lip standard strike, a 628 and 313 flat faceplate |
| 25AK41 (451-F-4RH-201-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS, Right Handed Deadlatch set that includes a 4502-01 short lip standard strike, a 628 and 313 flat faceplate |
| 25AK42 (451-F-4RH-101-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS, Right Handed Deadlatch set that includes a 4501-01 long lip standard strike, a 628 and 313 flat faceplate |
| 25AK43 (451-F-4LH-201-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS, Left Handed Deadlatch set that includes a 4502-01 short lip standard strike, a 628 and 313 flat faceplate |
| 25AK44 (451-F-4LH-101-628/313) | 1 $\frac{1}{2}$ " (38.1 mm) BS, Left Handed Deadlatch set that includes a 4501-01 long lip standard strike, a 628 and 313 flat faceplate |

Push / Pull Paddles - 459 Series



For use with the Ilco 451 series deadlatch. Functions as an alternate to knob or lever handles. Push or pull in the direction of the door swing to unlatch. Door Thickness: 1 $\frac{3}{4}$ " (44.45 mm)

Features:

- Corrosion resistant extruded aluminum construction, available in Aluminum or Dark Bronze finish
- Escutcheon is zinc alloy with a black hard coat finish for corrosion resistance
- Enhanced double spring construction for durability
- Four operation modes (Pull Left, Pull Right, Push Left, Push Right)
- Binder post insures secure attachment of the push/pull handle to the door
- Field reversible handing using cam plug and Push/Pull feature for added versatility
- Quality assured: Cycle testing exceeds ANSI Grade 1 standards

Grainger Item Numbers:

25AK45 (459-02-00-628)
25AK46 (459-02-00-313)
25AK47 (459-04-00-313)
25AK48 (459-04-00-628)

Push to the left, 628 finish
 Push to the left, 313 finish
 Push to the right, 313 finish
 Push to the right, 618 finish

Lever Handles - 456 Series



Levers are designed to keep fingers away from the jamb and allow operation without grasping. A downward movement retracts latch. For use with the Ilco 451 series deadlatch. Door Thickness: 1 $\frac{3}{4}$ " (44.45 mm) to 2" (50.8 mm)

Features:

- Available Left or Right Hand, handing easily reverse for versatility
- Durable Cast aluminum construction, aluminum or dark bronze finish
- Escutcheon assembly includes a $\frac{1}{4}$ " (6.35 mm) heat treated spindle

Grainger Item Numbers

25AK49 (456S-LH-01-AL)
25AK50 (456S-RH-01-AL)
25AK51 (456S-RH-01-DU)
25AK52 (456S-LH-01-DU)

Left Handed, Aluminum Finish
 Right Handed, Aluminum Finish
 Right Handed, Dark Bronze Finish
 Left Handed, Dark Bronze Finish



The Ilco 129 Rim Exit Devices are used on either single or double doors. When installing on double doors, a mullion (center piece) is required to enable the latch bolt, thus securing the door. All hardware is exposed. Applications include hollow metal, wood or aluminum doors. This style easily retro-fits existing doors with Jackson® 1295 exit devices.

Features:

- Meets ANSI Grade 1 requirements, UL Listed Life Safety
- Low profile push bar projects less than 3" (76.2 mm) from face of door
- Coated metal end caps protects against cart or equipment damage
- Non-Handed
- Two stock lengths: 36" (914.4 mm) and 48" (1219.2 mm)
- Easy access dogging system,
- Field sizable to 28" (711.2 mm) in width

Grainger Item Numbers:

25AK29 (129-3-313)

25AK30 (129-4-313)

25AK32 (129-4-628)

36" (914.4 mm) Rim, Dark Bronze Finish

48" (1219.2 mm) Rim, Dark Bronze Finish

48" (1219.2 mm) Rim, Clear Alum Finish