



**MCR
SAFETY**

4501

Welder

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety has the perfect welders glove to fit your individual needs. From premium options sewn with DuPont™ Kevlar® thread that provide maximum protection in conditions where users are exposed to heat, flame, and spark to rugged economical options that keep you safe and secure, we have you covered. With such a wide assortment to choose from, you are sure to Get Goin'! Light-R-Up with MCR Welders Gloves! The 4501 features blue regular split shoulder leather with a full sock jersey lining, cotton drill cuff lining and reinforced palm.

FEATURES:

- Rugged split shoulder leather, blue in color
- Full sock jersey lining
- Reinforced palm
- 13.5" 1 pc back
- Cotton drill cuff lining
- Sewn with DuPont™ Kevlar®



APPLICATIONS:

Automotive Assembly, Heliarc, Construction, Foundry, Mig/Tig, Ship building, Steel Work, Welding

TECHNICAL DATA FOR: 4501

Material Group	Leather	ANSI Contact Heat	Level 2 (Applications less than 284 degrees F)
Product Type	Welder		
Glove Size	X - Large		
Material	Leather		
Leather Cut	Split Select Shoulder		
Leather Type	Cow Skin		
Grade	Industrial Grade		
Insulated	Insulated		
Lining	Jersey		
Pattern	Gunn		
Thumb Style	Wing		
Thickness	1.1 - 1.6 mm		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

4501

Welder
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
4501	X - Large	13.625	6.500	5.250	60.246 lb.	10.041

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved