



WIHA TOOLS™

Item # 26X224

Mfr. Model # 32800

Set Includes:

Insulated Tool Set, 80 pc.

Rolling Case
Insulated Adjustable Wrench 8"
Insulated MaxiFlex Folding Ruler
Insulated Socket 3/8" Drive 7/8"
Insulated Hex L-Key 1/2" x 9.2"
Insulated SoftFinish Nut Driver 3/8, 1/4, 7/32, 7/16, 5/16"
Insulated SoftFinish Nut Driver 8.0, 5.0, 13.0, 10.0, 7.0, 5.5, 6.0mm
Insulated SoftFinish Slotted Screwdriver 8.0mm x 175mm, 3.0mm x 100mm, 3.5mm x 100mm, 4.5mm x 125mm, 10.0mm x 200mm, 6.0mm x 150mm, 5.5mm x 175mm, 2.5mm x 75mm
Insulated Hex L-Key 10.0mm x 220mm
Insulated Socket 3/8" Drive 1/2", 3/8" Drive 9/16", 3/8" Drive 5/8", 3/8" Drive 11/16", 3/8" Drive 3/4", 3/8" Drive 13/16, 3/8" Drive 22mm, 3/8" Drive 20mm, 3/8" Drive 19mm, 3/8" Drive 17mm, 3/8" Drive 15mm, 3/8" Drive 14mm, 3/8" Drive 13mm
Insulated Cable Stripping Knife 50mm
Insulated SoftFinish Xeno Driver #1 x 80mm
Insulated T-Handle Hex 7/32, 5/32, 5/16, 3/8, 3/16, 1/4"

Insulated T-Handle Hex 8.0, 6.0, 5.0, 4.0mm
Insulated SoftFinish Xeno Driver #2 x 100mm
Insulated SoftFinish Torx Screwdriver T25, T30, T20, T10, T7, T6, T15, T9, T8
Insulated SoftFinish Phillips Screwdriver #3 x 150mm, #1 x 80mm, #0 x 60mm, #2 x 100mm
Insulated Square Tip Screwdriver #1 x 100mm
Category IV Voltage Detector 110V
Insulated 3/8" Drive Extension Bar
Insulated Industrial Stripping Pliers 6.3"
Insulated Serrated Edge Cable Cutters 6.3"
Insulated Long Nose Pliers 8.0"
Insulated High Leverage Diagonal Cutter 8.0"
Insulated Square Tip Screwdriver #2 x 150mm
Insulated Diagonal Cutters 6.3"
Insulated Lineman's Pliers with Crimpers 9.0"
Insulated Long Flat Nose Pliers 6.3"
Insulated Bent Nose Pliers 6.3"
Insulated Long Nose Pliers 6.3"