



PADDLE MIXERS

Paddle mixers

Xo-R & Xo-R duo

This is not a modified drill.
It's a game changer
on the construction site.
Help you save your energy
and won't let you down when things get heavy.

> Features



· Ergonomically shaped handles ·



· Electronic switch ·



· HEXAFIX quick coupling ·



· Forced-action mixing effect* ·



· Rubber buffers ·



· Top quality ·

*only with Xo-R duo machines

Xo-R duo & Xo-R duo

- This machine won't let you down: Highest quality materials and finest German engineering for one of the most reliable products on the construction site. Proven hundreds of thousand times on construction sites all over the world.
- Collomix paddle mixers are designed for mixing. Every part of the machine is carefully engineered with this purpose in mind.
- Every material needs to be mixed with a suitable paddle. The quick coupling HEXAFIX® makes it easier than ever to change paddles in a second – completely tool-free.
- No more fatigue or even backaches from mixing. Whether it's the ergonomic handles or the optimized working height, Collomix paddle mixers are carefully designed to ensure the users health.
- No worries about dropping the machine accidentally or in a hurry. Rubber shock absorbers will prevent surfaces and the machine from being damaged. It will take much more to keep you from doing your work with a Collomix paddle mixer.
- Two Year Warranty



› Xo 6 R



› Xo 55 R duo

Technical data

	Xo 1 R	Xo 4 R	Xo 6 R	Xo 55 R duo
Rated power:	10.0 amps	11.8 amps	14.5 amps	13.1 amps
Voltage:	110 V	110 V	110 V	110 V
Gears:	1	2	2	1
On-load speed:	- 640 rpm	- 420 - 590 rpm	- 400 - 560 rpm	- 450 rpm
Spindle(s):	single	single	single	double (forced-action mixing)
Mixable quantity, recommended:	- 10 gal.	- 17 gal.	- 24 gal.	- 24 gal.
Cable length:	13 ft.	13 ft.	13 ft.	13 ft.
Weight with paddle:	12.3 lbs.	13,7 lbs.	15.4 lbs.	19.4 lbs.
Total paddle Ø:	4.75"	5.5"	6.25"	8.3"
Paddle set:	Type WK 120 HF for plaster, concrete, mortar, filler, etc.	Type WK 140 HF for plaster, concrete, mortar, filler, etc.	Type MK 160 HF for mortar of all kinds, concrete, quartz-filled epoxy resin mortar, etc.	Type MKD 140 HF for plaster, screed, mortar, multi-component materials, etc.
Art.no.	25105	25123	25147	25165

You name it,
.....
with the right paddle Xo-R mixes it.
.....

Heavy epoxy resin mortars, synthetic resin screeds, polymer coatings, concrete putty, restoration plasters, screed concrete, full thermal insulation, self-levelling compounds, dry mortars, pavement grouts, adhesive mortars, casting mortars and many more.

Collomix – your mixing partner. On the job for over 40 years.

Your Collomix specialised dealers:



Collomix North America | P.O. Box 13007 | Milwaukee, WI 53213 | Germany
info@collomix.de | www.collomix.com

