

Kellems® Wire Management Products

Features and Benefits

PolyTuff® I and PolyTuff® II Non-Metallic Liquidtight Conduit

All non-metallic construction ends fatigue and separation problems. They can be cut cleanly with a knife or PVC cutter so there are no jagged metal edges.



- PolyTuff® I Conduit, Gray**
- Rigid PVC core bonded to flexible PVC jacket
 - Approved for outdoor use and direct burial
 - UL Listed and CSA Certified



- PolyTuff® II Tubing, Black**
- PVC core with corrugated walls bonded to PVC jacket
 - Handles twists, turns, bends, switchbacks and straightaways with ease
 - UL Recognized and CSA Certified

PolyTuff® I Conduit

IP66
SUITABILITY



Trade Size (metric designator)	Feet (m)	Catalog Number
¾ (12)	100 (30.5)	G1038
	1200 (365.8)	G1038R1200
½ (16)	100 (30.5)	G1050
	1000 (304.8)	G1050R1000
¾ (21)	100 (30.5)	G1075
	800 (343.8)	G1075R800
1 (27)	100 (30.5)	G1100
	500 (152.4)	G1100R500
1¼ (35)	100 (30.5)	G1125
1½ (41)	50 (15.2)	G1150
2 (53)	50 (15.2)	G1200

Note: See pages X-58 and X-59, X-90 and X-91 for approved fittings.
See pages X-92 and X-93 for technical information and dimensional drawings.



PolyTuff® II Tubing

IP66
SUITABILITY



Trade Size (metric designator)	Feet (m)	Catalog Number
¼ (10)	100 (30.5)	B2025
¾ (12)	100 (30.5)	B2038
½ (16)	100 (30.5)	B2050
¾ (21)	100 (30.5)	B2075
1 (27)	100 (30.5)	B2100
1¼ (35)	100 (30.5)	B2125
1½ (41)	50 (15.2)	B2150
2 (53)	50 (15.2)	B2200

Note: See page X-90 for approved fittings.
See pages X-92 and X-93 for technical information and dimensional drawings.

