

# Product data sheet

## Characteristics

# 2510KR1

Switch, manual, 20A, 2 pole, 3 HP at 575 VAC, single phase, toggle operated, no indicator, NEMA 7&9, one conduit opening



### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Current Rating	20 A
Cable Entry	0.75 NPT (bottom)
Horsepower Rating	2 Hp 115 V AC 2 Hp 230 V AC 3 Hp 460 V AC 3 Hp 575 V AC 1 Hp 90 V DC 2 Hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Toggle
Number of Phases	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	6.36 in (161.54 mm)
Width	3.95 in (100.33 mm)
Depth	4.35 in (110.49 mm)

### Environment

Certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
NEMA Enclosure Rating	NEMA 3R/7/9 Cast Aluminium standard size

### Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	785901554639
Nbr. of units in pkg.	1
Package weight(Lbs)	3.46 lb(US) (1.57 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.69 in (11.9 cm)
Package 1 width	5.59 in (14.2 cm)
Package 1 Length	7.01 in (17.8 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------