

Product data sheet

Characteristics

2510KW2C

Switch, manual, 30A, 3 pole, 10 HP at 575 VAC, three phase, toggle operated, red 440/600 VAC indicator, NEMA 4 enclosure



Main

| | |
|---------|---------------------------|
| Product | Single Unit Manual Switch |
| Type | K |

Complementary

| | |
|------------------------|--|
| Current Rating | 30 A |
| Cable Entry | 0.75 NPT (bottom) |
| Horsepower Rating | 2 Hp 115 V AC 1 Hp 90 V DC 2 Hp 115 V DC 1.5 Hp 230 V DC 7.5 Hp 230 V AC 10 Hp 460 V AC 10 hp 575 V AC |
| Maximum Voltage Rating | 600 V AC 230 V DC |
| Number of Poles | 3P |
| Control Unit Type | Toggle |
| Number of Phases | 3 phase |
| Pilot Light | Red indicator, 440...600 V |
| Starter Type | Non reversing |
| Electrical Connection | Screw clamp terminals |
| Wire Gauge | AWG 14...AWG 10 copper |
| Height | 4.38 in (111.25 mm) |
| Width | 3 in (76.20 mm) |
| Depth | 4.56 in (115.82 mm) |

Environment

| | |
|-----------------------|---|
| Certifications | UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05 |
| NEMA Enclosure Rating | NEMA 4 die cast zinc alloy standard size |

Ordering and shipping details

| | |
|-----------------------|--------------------------|
| Category | 21102 - 2510,2511,2512 K |
| Discount Schedule | CP1 |
| GTIN | 785901436584 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.92 lb(US) (1.325 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 3.60 in (9.144 cm) |
| Package 1 width | 4.70 in (11.938 cm) |
| Package 1 Length | 5.40 in (13.716 cm) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Not compliant |
| China RoHS Regulation | China RoHS Declaration |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|