

Product data sheet

Characteristics

9999D20

Contacteur, Definite Purpose, auxiliary contact, 3A at 120 VAC, 2 NO contacts, for 50A to 90A DPA contactors



Main

Product Range	DPA
Component type	Auxiliary Contact Module
Used with	contacteur

Complementary

Auxiliary contact composition	2 NO
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.75 A 480 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A <= 600 V AC resistive control circuit UL 508

Environment

Product Certifications	CSA UL Recognized
------------------------	----------------------

Ordering and shipping details

Category	21762 - 9999 DISCOUNT CP1B
Discount Schedule	CP1B
GTIN	785901081319
Nbr. of units in pkg.	1
Package weight(Lbs)	1.44 oz (40.823 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.70 in (1.778 cm)
Package 1 width	1.80 in (4.572 cm)
Package 1 Length	3.70 in (9.398 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Weight	2.66 lb(US) (1.207 kg)
Package 2 Height	4.60 in (11.684 cm)
Package 2 width	4.60 in (11.684 cm)
Package 2 Length	10.40 in (26.416 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------