



Hasps

Lockout hasps are integral parts of a successful safety lockout program, providing effective multi-person lockout.

Safety Lockout Hasps

Lockout by Multiple Workers at Each Lockout Point

Attach hasp to energy disconnect switch

Control cannot be turned on until last worker's padlock is removed from hasp

Multiple styles available to fit most needs; **Spark resistant aluminum, Pry-resistant steel, Dielectric plastic, Dual jaw aluminum**

Model 427 – Labeled Snap-On Hasp

Combines multiple-person lockout and tagout identification

Features an easy-to-apply "snap-on" advantage with its spring-loaded locking arm

Fits more lockout points than alternative rivet-hinge labeled lockout hasps

Anodized aluminum and stainless steel construction for combined corrosion-resistance and strength

Complete with high visibility, re-usable, write-on safety labels (English, French & Spanish)

Aluminum



416

417

Heavy Duty Steel



418

419

Snap-On Aluminum

"Snap-On" Advantage



427

- 3WNZ9
- 3WNZ8
- 3WPA1
- 3WPA6
- 3WPA2
- 3WPA3
- 3WPA4
- 3WPA7

Dielectric



428

Steel



420

421

Dual Jaw Aluminum



429

Stainless Steel Hasp



S431

4mm Diameter Shackles Hasp



S430

Tabbed Steel



ALO80

ALO802

Master Lock Model #	Description	Inside Jaw Clearance	Jaw Dia.	Padlock Capacity
2CJH7	416 Spark Resistant Aluminum 1-1/2" x 4-3/8"	1"	1/4"	6
2CJH8	417 Spark Resistant Aluminum 2" x 4-7/8"	1-1/2"	1/4"	6
2CJH9	418 Heavy Duty Steel 2-3/8" x 3-1/4"	1"	1/4"	4
2CJJ1	419 Heavy Duty Steel 2-3/8" x 6-5/8"	1"	1/4"	8
1U177	420 Steel Jaw with Vinyl Coated Handle 1-3/4" x 4-1/2"	1"	1/4"	6
5T591	421 Steel Jaw with Vinyl Coated Handle 2-3/8" x 5"	1-1/2"	1/4"	6
2CJJ2	427 Red Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427AST Labeled Snap-On Hasp Assortment Pack (6 Hasps, Black, Blue, Green, Red, Silver, and Yellow)	1-3/4" x 2-1/8"	1/4"	5
	427BLK Black Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427BLU Blue Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427BRN Brown Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427CLR Silver Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427GRN Green Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427ORJ Orange Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427PRP Purple Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
	427YLW Yellow Labeled Snap-On Hasp 2-7/8" x 7"	1-3/4" x 2-1/8"	1/4"	5
4EMY3	428 Nylon Non-Conductive Hasp 1-5/8" x 6-7/8"	1" x 2-1/2"	3/16"	6
2CJJ3	429 Dual Jaw Aluminum Hasp 2" x 5-7/8"	1" & 1-1/2"	1/4"	8
4EMY4	AL080 Tabbed Steel Jaw with Vinyl Coated Handle 1-3/4" x 4-1/2"	1"	3/8"	6
2CJJ4	AL0802 Tabbed Steel Jaw with Vinyl Coated Handle 2-3/8" x 5"	1-1/2"	3/8"	6
	S430 4mm Steel Hasp with Red Plastic Handle 2-1/4" x 3"	1"	4mm	2
	S431 Stainless 316 Steel Hasp with 4mm diameter Shackle	1"	4mm	8