




Rebar Grounding Clamp, Perpendicular – EK17



- Universal use for rebar, rods or pipes
- Lay-in feature cuts installation time
- Bronze alloy construction with Stainless Steel 304 screws
- Approved for direct burial in earth and concrete



Part Number	EK17
Material	Bronze Stainless Steel 304 (EN 1.4301)
Connection Type	Perpendicular
Conductor Size	#10 Solid - #2 Solid 5.5 mm ² Stranded - 25 mm ² Stranded
Ground Rod Diameter, Actual (Ø)	0.5" – 1.0"
Water Pipe Size (Ø)	1/2" – 1"
Rebar Size, Metric	12 – 25 mm
Rebar Size, US	#4 – #8
Rebar Size, Canada	10M – 25M
Certifications	cULus Qualifoudre
Standard Packaging Quantity	50 pc
UPC	78285657558
EAN-13	8711893041705

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.